



FEATURES:

- Replaceable tip probe set includes a full set of ten replacement tips
- Replacement tips can be ordered separately, see model 6475.
- Designed for Fluke, Agilent, Tektronix and Wavetek-Meterman DMM's with a safety style sheathed banana jack.
- Probe incorporates a two-step mold process. First step is polypropylene for strength; second step is Santoprene® rubber for handling comfort, added insulation protection and wire strain relief.
- Probe and banana plug are molded directly onto the wire for robust pull strength.
- Wire is a high strand count silicone wire for extreme flexibility and high temperature resistance.
- Banana plug spring is nickel plated Beryllium Copper for long insertion life.

MATERIALS:

Probe: Outer Insulation: Santoprene® rubber, color: gray

Inner Insulation: Polypropylene, color: one black, one red

Tips: Gold plated Beryllium Copper, stainless steel, and Nickel plated brass

Wire: 18 AWG, Silicone insulation, length: 48"

Banana Plug: Nickel plated Brass

Spring: Nickel plated Beryllium Copper

Plug Insulation: Polypropylene, color: one black, one red

RATINGS:

IEC 1010-2-031, Category III 1000V

Operating Voltage: 1000 VRMS/DC

Current: 5 Amperes

ORDERING INFORMATION: Model 6474

Includes a set of one black and one red test leads with ten replaceable tips (two of each shown above)

All dimensions are in inches.

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Sales: 909-469-2900 Fax: 909-629-3317
Technical Assistance: 800-241-2060

PomonaACCESS 90869 (800) 444-6785 or (909) 469-2991
More drawings available at www.pomonaelectronics.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

6474