



FEATURES:

- True 75 Ohm connectors for optimal impedance match
- Highly flexible multi-stranded 75 Ohm RG59 type coax cable
- Red and Blue colored cables allow distinction between transmit and receive lines.

MATERIALS:

Connectors: BNC Male

Body: Brass, Tarnish resistant plating

Dielectric: PTFE

Center Contact – Gold Plated Brass

Strain Relief: PVC molded directly to cable and connectors

RATINGS:

Operating Voltage: Shield/Earth: 30VAC/60VDC Max.

Inner Conductor/Shield: 500VRMS Max.

Operating Temperature: +50°C (+122°F) Max.

ORDERING INFORMATION: Model 6510-V-XX-*

XX = Cable length, standard lengths = Black: 12" (304,8), 24" (609,8), 36" (914,4), 48" (1219,2), 60" (1524,0), Black, Red & Blue: 72" (1828,8)

*= Standard Color: 0-Black, 2-Red, 6-Blue

Ordering Example: Model 6510-V-48-2, Cable Length is 48" (1219,2) Color is Red

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[6510-V-600-0](#) [6510-V-240-0](#)