



FEATURES:

- Minigrabber® test clips attach to terminal sizes up to .060" diameter
- BNC connector is molded directly to the cable for pull strength durability and dust and moisture resistance
- Gold plated contacts for low noise connections
- Gold plated BNC center contact offers optimum corrosion resistance and low contact resistance to ensure test signal integrity

MATERIALS:

Kit contains one each Model 2449-C-48 and one each Model 3788

For full specifications, see data sheets for individual models

ORDERING INFORMATION: Model 6533

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02$ " (.51 mm), .xxx = $\pm .005$ " (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Pomona:](#)

[6533](#)