



FEATURES:

- 7 Piece set of BNC cables including one each: 1 ft., 2 ft., 3 ft., 4 ft., 5 ft., 6 ft. and 10 ft. lengths
- Molded flexible strain relief for heavy duty use
- Industry standard BNC connectors with gold plated contacts for low noise connections

MATERIALS:

Connectors: BNC Male

Body: Brass, tarnish resistant plating

Center Contact – Gold plated brass

Strain Relief: PVC molded directly onto cable and connectors

Marking: “Pomona 2249-C-XX”

(Where XX is the cable length in inches.)

RATINGS:

Operating Voltage: Shield/Earth: 30VAC/60VDC Max.

Inner Conductor/Shield: 500VRMS Max

Operating Temperature: +50°C (+122°F) Max

Nominal Impedance: 50 Ohms

ORDERING INFORMATION: Model 6534

(Replacement parts available: see model 2249-C)

All dimensions are in inches.

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Pomona:](#)

[6534](#)