



### FEATURES:

- For continuous use up to 400°F. (200°C.)
- Adhesive back Thermocouple will bond to almost any surface
- Available in “J” & “K” calibration

### MATERIALS:

“J” or “K” thermocouple mounted on a Kapton® surface.

### RATINGS:

Temperature Range: -20° to 200°C. (-4° to 400°F.)

### ORDERING INFORMATION: Model 6542X-XX

X = Calibration of Thermocouple “J” or “K” available

XX = Length in inches – Standard lengths 48” & 96”

Ordering Example: 6542K-96 is a “K” type calibration

Thermocouple with a length of 96 inches.

Kapton® is a registered trademark of E.I. Dupont Inc.

All dimensions are in inches. Tolerances (except noted): .xx = ±.02” (.51 mm), .xxx = ±.005” (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Sales: 800-490-2361 Fax: 888-403-3360  
Technical Assistance: 800-241-2060

PomonaACCESS 90974 (800) 444-6785 or (425) 446-6010  
More drawings available at [www.pomonaelectronics.com](http://www.pomonaelectronics.com)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

6542K-48