

Model 6733, 6734
Test Lead Wire with Silicone or PVC Insulation

Features

- Same wire as used with the Pomona test leads and patch cords.
- Make your own “Extra Long” test leads, jumpers or patch cords.
- Fits Pomona “Do-It-Yourself” banana plugs and jacks.
- High temperature and voltage ratings.
- Silicone insulation with high wire strand count allows for superb flexibility.
- Wear indication with double insulated (dual extruded) silicone leads shows white inner layer for increased safety.
- Wire will comply with International Safety Standard CAT III, IEC61010-031 requirements when correctly terminated with other components designed to meet CAT III, IEC61010-031 requirements.



Specifications:	6733	6734
Insulation:	Silicone	PVC
Length:	50 FT (15,2 meters)	50 FT (15,2 meters)
Wire size:	18 AWG	18 AWG
Wire:	192 X 41 bare copper	65 X 36 tinned copper
Diameter (OD):	.144" (3,60mm)	.144" (3,60mm)
Temperature:	-58° to +302°F (-50° to +150°C)	-4° to +221°F (-20° to +105°C)
Wire Rated Voltage:	10,000 DC *	5,000 DC *
Current:	20 A	15 A
Ordering Information:		
Black Wire:	6733-0	6734-0
Red Wire:	6733-2	6734-2
* Hands free testing in controlled voltage environment: <i>For CE compliance:</i> not intended for hand held use at voltages above 30 Vrms / 42.2 Vpk / 60 Vdc or when current exceeds 8A maximum.		

USA: Sales: 800-490-2361
 Technical Support: technicalsupport@pomonatest.com
 Fax: 425-446-5844
Europe: 31-(0) 40 2675 150 **International:** 425-446-5500
Where to Buy: www.pomonaelectronics.com

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm). All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[6734-2](#) [6734-0](#) [6733-0](#) [6733-2](#)