


**Model 73043**  
**BNC Plug, 50 Ohm, Crimp Type, RG8, 9, 11, 213, 214**



*Model 73043*  
*BNC Plug, 50 Ohm, Crimp Type,*  
*RG8, 9, 11, 213, 214*

**Features**

- DC – 2GHz bandwidth.
- Connectors are precision machined.
- Connector accepts cable types RG/U: 8, 9, 11, 213, 214

**Materials**

Center Conductor, Male: Phosphor Bronze, Gold Plated  
Connector Body: Brass, Nickel Plated  
Crimp Ferrule: Brass, Nickel Plated  
Insulators: PTFE

**Specifications**

Impedance: 50Ω  
Frequency Range: DC – 2GHz  
Contact Resistance:  
Center Conductor: ≤1.5 mΩ  
Outer Conductor: ≤0.2 mΩ  
Insulation Resistance: ≥ 5000 MΩ  
Dielectric Withstand Voltage: 1500V  
*For CE compliance, do not hold in hand when voltages exceed 33 Vrms / 70 Vdc.*  
Number of Insertions: 500 cycles minimum

**Ordering Information**

Model: **73043**

USA: Sales: 800-490-2361  
Technical Support: [technicalsupport@pomonatest.com](mailto:technicalsupport@pomonatest.com)  
Fax: 425-446-5844

Europe: 31-(0) 40 2675 150 International: 425-446-5500

Where to Buy: [www.pomonaelectronics.com](http://www.pomonaelectronics.com)

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ± .005" (.127 mm). All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies.

**Model 73043**  
**BNC Plug, 50 Ohm, Crimp Type, RG8, 9, 11, 213, 214**

**Cable Types and Crimp Die Information**


Connector Model #	Cable Groups	Crimp Die Cavity Size for Outer Ferrule
73043	RG8, 9, 11, 213, 214	.429 (10.9)

**Cable Assembly Instructions**


1. CUT CABLE END EVENLY AND PERPENDICULAR.




2. SLIDE FERRULE OVER AND SHRINK TUBING OVER CABLE.




3. STRIP CABLE JACKET, BRAID AND DIELECTRIC TO SPECIFIC LENGTHS.






4. FLARE BRAID END SLIGHTLY.



5. CRIMP CENTER CONTACT ONTO CENT COUDUCTOR.



6. SLIDE CONNECTOR BODY UNDER BRAID. SLIDE FERRULE OVER BRAID AND CRIMP. SLIDE SHRINK TUBING OVER CRIMP AND SHRINK.



**USA:** Sales: 800-490-2361  
 Technical Support: [technicalsupport@pomonatest.com](mailto:technicalsupport@pomonatest.com)  
 Fax: 425-446-5844  
**Europe:** 31-(0) 40 2675 150 **International:** 425-446-5500  
**Where to Buy:** [www.pomonaelectronics.com](http://www.pomonaelectronics.com)

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm). All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Pomona:](#)

[73043](#)