



FEATURES:

- Features flex boots for insulation protection.
- Alligators are nickel plated for tarnish resistance.
- Alligator clip has .187" (4.75mm) max. jaw opening.
- Ideal for use as a temporary wire.

MATERIALS:

Alligator:

Body: Steel, Nickel Plated

Spring: Stainless Steel

Flex Boot: Vinyl

Wire:

(Model 1236) 20 AWG, Stranding: 41 x 36 tinned copper, PVC Insulation, .087" (2.21 mm) O.D.

Marking: "POMONA 1236-XX"

(Model MG-B) 18 AWG, Stranding: 65 x 36 tinned copper, PVC Insulation, .144" (3.66 mm) O.D.

Marking: "POMONA MG-B-XX"

RATINGS:

Operating Voltage: 33VRMS/70VDC MAX

Operating Temperature: +50°C (+122°F)

Current: 5 Amperes

ORDERING INFORMATION: XX = Length in inches

Model 1236-XX-*

Standard Lengths: 24" (60.96mm)

Additional lengths can be quoted upon request.

Model MG-B-XX-*

Standard Lengths: 12" (30.48mm), 24" (60.96mm)

Additional lengths can be quoted upon request.

* = Color of Flex Boot and Wire, -0 Black, -2 Red

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[MG-B-4-2](#) [MG-B-24-2](#) [MG-B-24-0](#) [MG-B-12-2](#) [MG-B-12-0](#)