



FEATURES:

- Ideal for use as a temporary jumper wire.

MATERIALS:

Conn: Insulated Microgator Clip

Material: Solid copper.

Insulation: Vinyl.

Color: Matches color of wire.

Wire: 20 AWG stranding 41 x 36 t.c., PVC insulated, 2.21 (.087) O.D.

Marking: "POMONA 1613-XX"

RATINGS:

Operating Temperature: +50°C. (+122° F.) Max.

Operating Voltage: Hand-held testing: 30VAC/60VDC Max.

Current: 5 Amperes

ORDERING INFORMATION: Model 1613-XX-*

XX = Cable Lengths, Standard Lengths: 4" (102), 8" (203), 12" (305), 18" (457), 24" (610), 36" (914), 48" (1219) & 60" (1524). Additional lengths and colors can be quoted upon request.

*= Color, -0 Black, -2 Red

Ordering Example: 1613-60-2 Indicates 60" in length, color is Red

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ± .005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[1613-4-2](#) [1613-4-0](#) [1613-36-2](#) [1613-36-0](#) [1613-48-2](#) [1613-48-0](#) [1613-8-0](#) [1613-8-2](#) [1613-24-2](#) [1613-24-0](#) [1613-12-0](#) [1613-12-2](#)