



FEATURES:

- Alligator Clip features a banana jack interface for quick and easy attachment to various lengths of banana plug patch cords.
- Alligator jaw opens up to .300" (7,62mm) for attachment to most test terminals.
- Alligator is gold plated for low contact resistance.
- Flexible boot provides insulation protection.

MATERIAL:

Alligator: Gold Plated

Flexible Boot: Vinyl, Color per Part Number

RATING:

Operating Temperature: +50° C (+122° F)

Voltage: 150 VRMS

Current: 5 Amperes Max.

ORDERING INFORMATION: Model 3289-*

= Color Code, -0 Black, -2 Red

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ± .005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[3289-2](#) [3289-0](#)