



FEATURES:

- Mates to Model #PT080 or any standard 0.080" pin tip plug.
- Alligator clip has 4.7 (.187) Max. jaw opening.

MATERIALS:

Minigator Clip:

Material: Steel

Finish: Nickel plated

Insulator:

Material: Vinyl

2.03 (.080) Dia. – Pin Tip Jack

Material: Jack Body – Brass per QQ-B-626, Alloy 360, ½ Hard.

Spring – Beryllium Copper per QQ-C-533, Alloy 172, Cond. HT

Finish: Gold plated per MIL-G-45204, Type II, Class 00 over electroless nickel.

RATINGS:

Operating Temperature: +50°C. (+122°F.) Max.

Operating Voltage: 45 VRMS/DC

Current: 5 Amperes

ORDERING INFORMATION: Model 3491-*

*=Color, -0 Black, -2 Red

Ordering Example: 3491-2 Color is Red

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[3491-2](#) [3491-0](#)