



MATERIALS:

Body and Coupling Nut: Gold Plated Beryllium Copper per QQ-C-530, Cond. HT

Center Contact: Gold Plated Brass

Insulation: Teflon per L-P-403

Finish: Body, Coupling Nut and Contact: Gold Plated Brass per MIL-G-45204, Type II, Class 2

RATINGS:

Operating Temperature: -65°C. (-85°F.) to +165°C. (+329°F.)

Operating Voltage: 1000 VRMS, 60 Hz at sea level

Insulation Resistance: 5000 Megohms Min.

ORDERING INFORMATION: Model 4283

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies.

Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

4283 4283A