



MATERIALS:

Box and Cover: Glass filled nylon. Color: Blue

Marking: 4384

Screw: 4 Ea. Pan Head, self-tapping #2-32 cover crews. Carbon Steel.

Finish: Blue Zinc Plated

RATINGS:

Operating Temperature: +102°C. (+216°F.) Max.

ORDERING INFORMATION: Model 4384-*

*=Color Code, -0 Black, -6 Blue

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).
All specifications are to the latest revisions. Specifications are subject to change without notice.
Registered trademarks are the property of their respective companies.

Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[4384-6](#) [4384-0](#)