



MATERIALS:

Contact – Beryllium Copper, Alloy 165, ½ HM.

Spring – Stainless Steel, 302

Sq. Pin – Phosphor Bronze, Alloy 510

Finish:

Contact & Sq. Pin – Gold plated per MIL-G_45204, Type II, Class 00 over nickel.

Insulation: Glass filled nylon.

Marking: “POMONA GRABBER® 4521”

Overall Length: 1.73”

RATINGS:

Operating Temperature: +102°C. (+216°F.) Max.

Operating Voltage: 150 VRM/DC

Current: 3 Amperes

ORDERING INFORMATION: Model 4521-* & Model 5925 Kit

* = Color, Standard Colors: -0 Black, -2 Red

Kit 5925 contains 10 pieces of 4521 clips, one of each color: -0 Black, -1 Brown, -2 Red, -3 Orange, -4 Yellow, -5 Green, -6 Blue, -7 Violet, -8 Gray, -9 White

All dimensions are in inches. Tolerances (except noted): .xx = ±.02” (.51 mm), .xxx = ±.005” (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies.

Made in USA

6/9/99

SY/EH/LS

W:\pomona\grponly\Datasheet Updates\Updates 2005\d4521_K5925_1_02.doc

More drawings available at www.pomonaelectronics.com

Page 1 of 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[4521-1](#) [4521-3](#) [4521-4](#) [4521-5](#) [4521-6](#) [4521-7](#) [4521-8](#) [4521-9](#)