



### MATERIALS:

Body and Fittings – Stainless Steel

Center Contact – Beryllium Copper

Dielectric – Teflon

Finish: Body and Center Contact – Gold Plated

### RATINGS:

Operating Temperature: -65°C (-85°F) to +165°C (+329°F)

Operating Voltage: 335 VRMS

Nominal Impedance: 50 Ohms

Frequency Range: DC to 18 GHz

Connectors meet the interface requirement of MIL-C-39012

### ORDERING INFORMATION: Model 4850

All dimensions are in inches. Tolerances (except noted): .xx =  $\pm$ .02" (.51 mm), .xxx =  $\pm$ .005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies.

Made in USA

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

4850