



MATERIALS:

Body and Fittings: Brass per QQ-B-626, Alloy 360, 1/2 hard

Center Contacts: Gold Plated Beryllium Copper per QQ-C-530, Cond. HT.

Dielectric: PTFE

Finish:

Body and Fittings: Tarnish Resistant

Center Contacts: Gold plated per requirements of MIL-C-39012

Marking: "POMONA 4940"

RATINGS:

Operating Voltage: 500 VRMS

Nominal Impedance: 50 Ohms

ORDERING INFORMATION: Model 4940

All dimensions are in inches. Tolerances (except noted): .xx = ± 0.02 " (.51 mm), .xxx = ± 0.005 " (.127 mm).
All specifications are to the latest revisions. Specifications are subject to change without notice.
Registered trademarks are the property of their respective companies.

Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

4940