



### MATERIALS:

Body: Brass, Tarnish Resistant Plating

Alloy 360, ½ Hard or Phosphor Bronze

Male Contact: Gold Plated Brass

Female Contact: Gold Plated Beryllium Copper

Dielectric: PTFE

Finish:

Body and Fittings: Tarnish resistant

Male and Female Contact – Gold plated

Marking: “POMONA 4958”

### RATINGS:

Operating Temperature: -65°C (-85°F) to +165°C (+329°F)

Operating Voltage: 500 VRMS Max.

Nominal Impedance: 50 Ohms

### ORDERING INFORMATION: Model 4958

All dimensions are in inches. Tolerances (except noted): .xx = ±.02” (.51 mm), .xxx = ± .005” (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies.

Made in USA

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Pomona:](#)

[4958](#)