



MATERIALS:

Tip: Stainless Steel, Type 410

Probe Cap & Body: Nylon 6

Wire: 20 AWG., PVC., 2,21 (.087) O.D.

Banana Plug Housing: Polypropylene

Banana Plug: Brass, Nickel plated

RATINGS:

Operating Temperature: +55°C. (+131°F.) Max.

Operating Voltage: 1000V

Current: 5 Amperes Max.

ORDERING INFORMATION: Model 5950

Set of two 48" long PVC insulated leads, one black and one red

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

5950