



Features:

- ✓ Adapter allows two F type male connectors to connect together, stand alone or through a bulkhead/panel.
- ✓ Maximum bulkhead or panel thickness: .250" (6,35).
- ✓ Adapter is precision machined (not die-cast) from brass.

Materials:

Connector Body	Nickel plated brass
Center Contact	Nickel plated brass
Insulator	Polystyrene

Ratings:

Impedance:	75 Ohms
Frequency:	0 to 500 MHz
VSWR:	1.5 max
Contact Resistance:	3 Milliohms max.
Voltage	* 500 V
Insulation Resistance:	5,000 Megohms min.
Insertions:	500
Temperature:	-40 to +65 C

* *Hands free testing* in controlled voltage environment: *For CE compliance:* not intended for hand held use at voltages above 33 Vrms / 70 Vdc.

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Sales: 800-490-2361 Fax: 888-403-3360 Technical Assistance: 800-241-2060
For "Where to Buy" information, visit the Pomona web site at www.pomonaelectronics.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

6706