



### MATERIALS:

Model **5907A**: Test Lead Straight to Right Angle: Banana Spring: Nickel plated Beryllium Copper, Insulation–Polypropylene, fire retardant, UL94 V-2, Wire: 48" silicone 18" AWG, Color: One Black, One Red, **RATINGS:** 1000 VRMS, 10 Amperes.

Model **5910A**: Maxigrabber set with Pincer Tip - **RATINGS:** 1000 VRMS, 10 Amperes, CAT III, P2

Model **5912A**: Maxigrabber Alligator Clip - **RATINGS:** 1000 VRMS, 10 Amperes, CAT III, P2

Model **5916A**: Medium Alligator Clip: Body–Steel, Nickel plated, Insulation–Polypropylene, fire retardant, UL94 V-2, Color: One Black, One Red, **RATINGS:** 300 VRMS, 5 Amperes.

Model **6035**: Fully Insulated Switchable Oscilloscope Probes, **RATINGS:**

### Performance Specifications:

| Attenuation: | Bandwidth (MHz) | Input Impedance (MW) | Input Capacitance (pF) | Approx. Rise Time (nS) | Voltage (V Max.) + | Compensation Range (pF) | Cable Length: |
|--------------|-----------------|----------------------|------------------------|------------------------|--------------------|-------------------------|---------------|
| X1/X10       | 20/200          | 1/10                 | 47/15                  | 17.5/1.8               | 250                | 10-60                   | 1.2 Meters    |

+ Derated with Frequency

Model **6041A**: Ex-Large Alligator Clip: Body–Steel, Nickel plated, Insulation–Nylon 6, fire retardant, UL94 V-O, Torsion spring-music wire, Color: One Black, One Red, **RATINGS:** 1000 VRMS, 10 Amperes

Model **6232**: Test Probe: Insulation – Polypropylene, fire retardant, UL94 V-2 rated, Probe Tip – Brass, nickel plated,

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

## Model 6120 Deluxe Test Companion Kit For Fluke ScopeMeter®

4mm safety jack: brass, nickel plated, Color: One Black, One Red, **RATINGS:** 1000 VRMS, 10 Amperes.

**ORDERING INFORMATION:** Model 6120 (Includes a kit of items from above)

Replacement P/N's: Model **5907A**: Test Lead Straight to Right Angle, Model **5910A**: Maxigrabber set with Pincer Tip, Model **5912A**: Medium Alligator Clip, Model **5916A**: Medium Alligator Clip: Body-Steel, Nickel plated, Insulation-Nylon 6, fire retardant, UL94 V-O, Color: One Black, One Red, **RATINGS:** 300 VRMS, 5 Amperes, Maxigrabber Alligator Clip, Model **6035**: Fully Insulated Switchable Oscilloscope Probes Model **6041A**: Ex-Large Alligator Clip, Model **6232**: Test Probe.

All dimensions are in inches. Tolerances (except noted): .xx =  $\pm .02$ " (.51 mm), .xxx =  $\pm .005$ " (.127 mm).  
All specifications are to the latest revisions. Specifications are subject to change without notice.  
Registered trademarks are the property of their respective companies. Made in USA

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

6120