



TIME-10 Process Control Stopwatch

Optimize process phases by analyzing and precisely timing each task. When improving process flow, verify improvement times and cost savings on production floors or assembly lines with precise stopwatches.

- Chronograph: 1/100 stop watch, split/lap time
- Time display: hour, minute, second, day, week day, month and year
- Alarm function
- Hourly chime
- Water resistant

No hassle warranty

No waiting.

*No shipping
charges.*



Our commitment to high-quality products and customer service is demonstrated by our industry exclusive "No Hassle" warranty. In the unlikely event that an Amprobe Test Tool requires warranty service, any of our local dealers are authorized to replace it, on the spot.

(note: \$500 MSLP limit)





TIME-10 Process Control Stopwatch

Data Sheet

Specifications

Normal Time	Days, Month, Date, Hour, Minute, Second, AM/PM, 12/24 Hours, Alarm Sign Hourly Chime
Alarm Time	Hour, Minute, Alarm Sign Hourly Chime
Chronograph	1/100 Stop watch
	Max Count: 50:59 (Minute : Second) (99/100Sec)
Water Resistant	Yes
Dimensions	65(L) x 56(W) mm (2.56 x 2.20 in)
Weight	Approx. 47 g (0.10 lb)
Battery	LR44

Amprobe® Test Tools

website: www.Amprobe.com
email: info@amprobe.com
Everett, WA 98203
Tel: 877-AMPROBE

Amprobe® Test Tools Europe

In den Engematten 14
79286 Glottertal, Germany
Tel.: +49 (0) 7684 8009 - 0

©2009 Amprobe Test Tools. All rights reserved.
7/2009 3520551 Rev A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[AMPROBE:](#)

[TIME-10](#)