



MATERIALS:

Body: Brass, White Bronze Plating

Center Contact: Gold Plated Beryllium copper

Dielectric : PTFE

Finish: Body – Tarnish resistant

Center Contact – Gold Plated

Marking: “POMONA 4956” located approximately as shown.

RATINGS:

Operating Voltage: 1000 VRMS

Impedance: 50 Ohms

ORDERING INFORMATION: Model 4956

All dimensions are in inches. Tolerances (except noted): .xx = ±.02” (.51 mm), .xxx = ± .005” (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies.

Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

4956