



FEATURES:

- Permits phono plug to be used with equipment having BNC females.
- All metal construction to insure proper shielding.

MATERIALS:

Upper Conn: Phono Jack.

Material: Brass.

Finish: Nickel plated.

Lower Conn: BNC Male.

Finish: Body and fittings, tarnish resistant.

Center Contact: Gold Plated per requirements of MIL-C-39012.

Nominal Impedance: 50 Ohms.

Marking: "POMONA 4054"

RATINGS:

Operating Temperature: +125°C (+257°F) Max.

Operating Voltage: 500 Max.

ORDERING INFORMATION: Model 4054

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

4054