



### FEATURES:

- Provides a method for Spade Lugs, Banana Plugs or .080" Tip Plugs to interface with a BNC Jack
- The high voltage connector allows usage above the standard BNC voltage

### MATERIALS:

Body:

Insulation: ABS Plastic

Binding Post: Nickel plated brass

Binding Post Collar:

Insulation: Polycarbonate

Body: Electroless nickel plated brass

### RATINGS:

Operating Voltage: 5000V Peak

Operating Temperature: +50°C (+122°F) Max.

### ORDERING INFORMATION: Model 3291

All dimensions are in inches and metric. All specifications are to the latest revisions. Specifications are subject to change without notice.  
Registered trademarks are the property of their respective companies. Made in USA

Sales: 800-490-2361 Fax: 888-403-3360  
Technical Assistance: 800-241-2060

PomonaACCESS 90812 (800) 444-6785 or (425) 446-6010  
More drawings available at [www.pomonaelectronics.com](http://www.pomonaelectronics.com)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

3291