



FEATURES:

- Interfaces to Pomona's .025" (.64mm) Square Pin Micrograbber (Model 4521), Rotating Micrograbber, (Model 5790), SMD Grabber (Model 5360) and Minigator (Model 5363).
- Ideal for jumping .025" (.64mm) Square Pins on PC Test Boards.
- Receptacle is gold plated to optimize the electrical connection.

MATERIALS:

Receptacle Body – Phosphor Bronze, Gold Plated

Housing: Polypropylene, Color Matches Wire

Wire: 22 AWG, 26 x 36 t.c., PVC Insulation .064" (1,63mm) O.D. Nom.

Color per part number

RATINGS:

Operating Temperature: +50°C (+122°F)

Operating Voltage: 45 VRMS

Current: 3 Amperes Max.

ORDERING INFORMATION: Model 4741-XX-*

XX = Length in Inches, Standard Lengths: 6" (15,24cm), 12" (30,48cm), 24" (60,96cm), 36" (91,44cm)

* = Color, Standard Colors: -0 Black, -1 Brown, -2 Red, -3 Orange, -4 Yellow, -5 Green, -6 Blue, -7 Violet, -8 Gray, -9 White

Model 5948

Kit contains 1 each of 10 colors of 4741-6

All dimensions are in inches and metric. All specifications are to the latest revisions. Specifications are subject to change without notice.
Registered trademarks are the property of their respective companies. Made in USA

Sales: 800-490-2361 Fax: 888-403-3360
Technical Assistance: 800-241-2060

PomonaACCESS 90415 (800) 444-6785 or (425) 446-6010
More drawings available at www.pomonaelectronics.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Pomona:](#)

[4741-12-2](#)