



FEATURES:

- Mate to Model #3542, 4773 or any other standard .08 inch pin jack.
- Ideal for use as jumper wires on chassis boxes.

MATERIALS:

Conn: Pin Tip Plug

Material: Brass Per QQ-B-626, Alloy 360, ½ Hard.

Finish: Gold plated per MIL-G-45204, Type II, Class 00 over electroless nickel per MIL-C-26074, Class I, 200/300 microinches.

Insulation: Polypropylene molded to plug body and wire.

Color: Matches color of wire.

Marking: "POMONA ELECTRONICS CALIF."

Wire: 22 AWG, stranding 19 x 34, t.c., PVC insulated, 1.63 (.064) O.D.

Color: See Ordering Information.

Marking: "POMONA PT080-XX"

RATINGS:

Operating Temperature: +55°C (+131°F) Max

Operating Voltage: 1000 WVDC

Current: 3 Amperes Cont.

ORDERING INFORMATION: Model PT080-XX-*

XX = Cable Lengths, Standard Lengths: 8" (203mm)

Additional lengths can be quoted upon request.

*= Color, -0 Black, -2 Red

Ordering Example: PT080-8-2, Indicates 8" in length, Color is Red

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies.

Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[PT080-8-2](#) [PT080-8-0](#)