



### MATERIALS:

Body/Fittings: Brass, Tarnish Resistant Plating, Alloy 360, 1/2 Hard  
 Center Contact: Gold Plated Beryllium Copper  
 Dielectric: PTFE  
 Gasket: Silicon Rubber per ZZ-R-765, Class II, Grade 50  
 Marking: "POMONA 5178"

### RATINGS:

Operating Voltage: 500 VRMS

### ORDERING INFORMATION: Model 5178

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).  
 All specifications are to the latest revisions. Specifications are subject to change without notice.  
 Registered trademarks are the property of their respective companies.

Made in USA

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

5178