




CXF4



CXF4(L)6-60V



CXF4(L)110-240V



Dimensions

Width	6 mm	6 mm	6 mm
Length	65.4 mm	65.4 mm	65.4 mm
Height w/ DIN Rail	35 x 7.5 mm 35 x 15 mm	61.3 mm 68.8 mm	61.3 mm 68.8 mm

Technical Data/Ratings

Approvals	   	   	   	   		
Wire Size (solid stranded)	24-10 AWG	0.2-4 mm ²	24-10 AWG	0.2-4 mm ²	24-10 AWG	0.2-4 mm ²
Voltage Rating	600 V	1000 V	600 V	1000 V	600 V	1000 V
Current Rating	10 A	10 A	10 A	10 A	10 A	10 A
Insulation Material	Polyamide 66		Polyamide 66		Polyamide 66	

Fuse Specifications

Fuse Type	5x20 mm	5x20 mm	5x20 mm
LED Indicator Voltage	—	6-60V AC/DC	110-240V AC/DC

Installation Instructions


Wire Stripping Length	10 mm	10 mm	10 mm
Screwdriver	0.6x3.5 mm	0.6x3.5 mm	0.6x3.5 mm

Terminal Blocks


	Cat. No.	Std. Pk.	Cat. No.	Std. Pk.	Cat. No.	Std. Pk.
Grey (standard)	CXF4	50	CXF4(L)6-60V	50	CXF(L)110-240V	50
Blue BU	CXF4/BU	50	CXF4(L)6-60V/BU	50	CXF4(L)110-240V/BU	50
Black BL	CXF4/BL	50	CXF4(L)6-60V/BL	50	CXF4(L)110-240V/BL	50

Accessories

End Plate	—	—	—	—	—	—
Partition Plate	PPCX4/3	20	PPCX4/3	20	PPCX4/3	20
DIN Rail	2511120 CA701-15/S	20 10	2511120 CA701-15/S	20 10	2511120 CA701-15/S	20 10
End Stop	CA702 CA802 CA103	50 50 50	CA702 CA802 CA103	50 50 50	CA702 CA802 CA103	50 50 50
Shorting Link/ Jumpers	2 pole JX4/2 3 pole JX4/3 4 pole JX4/4 10 pole JX4/10	100 50 50 10	JX4/2 JX4/3 JX4/4 JX4/10	100 50 50 10	JX4/2 JX4/3 JX4/4 JX4/10	100 50 50 10
Warning Label	WLX4	100	WLX4	100	WLX4	100
Test Plug	TX4	50	TX4	50	TX4	50
Marking Tag	MT6	100	MT6	100	MT6	100



LED Circuit for offline indication in CXF4L6-60V



LED Circuit for offline indication in CXF4L110-240V

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Altech:](#)

[CXF4](#) [CXF4/BL](#) [CXF4\(L\)110-240V](#) [CXF4/BU](#) [CXF4\(L\)6-60V/BU](#) [CXF4\(L\)6-60V/BL](#) [CXF4\(L\)110-240V/BL](#)
[CXF4\(L\)110-240V/BU](#) [CXF4/3](#) [CXF4/3L110-240V](#) [CXF4/3L6-60V](#)