

CY SERIES

SCREW TERMINAL BLOCKS

HIGHLIGHTS

FEATURES



- 2 connection grounding terminals
- Yellow/ Green Color as per Industry standard
- Snap-on feet

APPLICATIONS


- Grounding Applications

GROUND / EARTH TERMINAL BLOCKS


CYG2.5



CYG4



CYG6



Dimensions & Weight

	CYG2.5	CYG4	CYG6
Width	5 mm	6 mm	8 mm
Length	50 mm	50 mm	50 mm
Height w DIN Rail	35 x 7.5 mm 35 x 15 mm	49 mm 56.5 mm	49 mm 56.5 mm
Weight per piece	11.7 g	13.7 g	22.9 g

Technical Data/Ratings

Approvals						
Wire Size (solid stranded)	24-12 AWG		0.2-2.5 mm ²		24-10 AWG	
Voltage Rating	600 V		1000V AC/DC		600 V	
Current Rating	—		—		—	
Torque	3.6 lb.in		0.4 Nm		4.5 lb.in	
Insulation Material	Polyamide 66		Polyamide 66		Polyamide 66	

Installation Instructions

Wire Stripping Length	8 mm	9 mm	10 mm
Screwdriver	Flat Head 0.5 x 3 mm	Flat Head 0.6 x 3.5 mm	Flat Head 0.8 x 4 mm


Terminal Blocks

	Cat. No.	Std. Pk.	Cat. No.	Std. Pk.	Cat. No.	Std. Pk.
Yellow / Green	CYG2.5	100	CYG4	100	CYG6	100

Accessories

Accessories		Cat. No.	Std. Pk.	Cat. No.	Std. Pk.	Cat. No.	Std. Pk.
End Plate		EPCY2.5/10	50	EPCY2.5/10	50	EPCY2.5/10	50
Partition Plate		PPCY2.5/10	20	PPCY2.5/10	20	PPCY2.5/10	20
DIN Rail		2511120	50	2511120	50	2511120	50
		CA701-15/S	50	CA701-15/S	50	CA701-15/S	50
End Stop		CA702	50	CA702	50	CA702	50
		CA802	50	CA802	50	CA802	50
		CA103	50	CA103	50	CA103	50
Shorting Link/ Jumpers		JX2.5/2	100	JX4/2	100	JY6/2	100
		JX2.5/3	50	JX4/3	50	—	—
		JX2.5/4	50	JX4/4	50	—	—
		JX2.5/5	50	—	—	—	—
		JX2.5/6	50	—	—	—	—
		JX2.5/7	10	—	—	—	—
		JX2.5/8	10	JX4/8	10	—	—
		JX2.5/10	10	JX4/10	10	—	—
		—	—	JX4/16	10	—	—
Marking Tag		MT5	1 Pk. (100 tags)	MT6	1 Pk. (100 tags)	MT8	1 Pk. (100 tags)
Warning Label		WLX2.5	100	WLX4	100	WLX6	100

CYG10



Dimensions & Weight

Width	10 mm
Length	50 mm
Height w DIN Rail	49 mm
35 x 7.5 mm	56.5 mm
35 x 15 mm	
Weight per piece	30.1 g

Technical Data/Ratings

Approvals	
Wire Size (solid stranded)	24-6 AWG 0.2-10 mm ²
Voltage Rating	600 V 1000V AC/DC
Current Rating	— —
Torque	14 lb.in 1.2 Nm
Insulation Material	Polyamide 66

Installation Instructions


Wire Stripping Length	11 mm
Screwdriver	Flat Head 0.8 x 4 mm

Terminal Blocks

	Cat. No.	Std. Pk.
Yellow / Green	CYG10	50

Accessories

End Plate		EPCY2.5/10	50
Partition Plate		PPCY2.5/10	20
DIN Rail		2511120	50
		CA701-15/S	50
End Stop		CA702	50
		CA802	50
		CA103	50
Shorting Link/ Jumpers	2 pole 3 pole 4 pole 5 pole 6 pole 7 pole 8 pole 10 pole 16 pole	JY10/2 — — — — — — — — —	20 — — — — — — — — —
Marking Tag Warning Label		MT10 WLX10	1 Pk. (100 tags) 100



CYG4 Ground Block Assembly

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Altech:](#)

[CYG10](#) [CYG2.5](#) [CYG4](#)