




Blade/ Knife Style Disconnect Terminal Blocks



CYK4



CYDLK4



CYDLGK4



Dimensions & Weight

Width	6 mm	6 mm	6 mm
Length	58.8 mm	94.5 mm	94.5 mm
Height w/ DIN Rail	35 x 7.5 mm 35 x 15 mm	51.5 mm 56.6 mm	67.6 mm 75.1 mm
Weight per piece	13.3 g	27.5 g	32.9 g

Technical Data/Ratings

Approvals 	 E220514	 60947-7-1	 E220514	 60947-7-1	 E220514	 60947-7-1
Wire Size (solid / stranded)	24-10 AWG	0.2-4 mm ²	24-10 AWG	0.2-4 mm ²	24-10 AWG	0.2-4 mm ²
Voltage Rating	600 V	1000V AC/DC	300 V	630V AC/DC	300 V	500V AC/DC
Current Rating Disconnect (Top)	26 A	28 A	26 A	20 A	26 A	20 A
Current Rating Feed Thru (Mid)	—	—	30 A	30 A	30 A	30 A
Torque	4.5 lb-in	0.5 Nm	4.5 lb-in	0.5 Nm	4.5 lb-in	0.5 Nm
Insulation Material	Polyamide 66		Polyamide 66		Polyamide 66	

Installation Instructions

Wire Stripping Length	10 mm	8 mm	8 mm
Screwdriver	Flat Head 0.5 x 3 mm	Flat Head 0.6 x 3.5 mm	Flat Head 0.8 x 4 mm

Terminal Blocks


	Cat. No.	Std. Pk.	Cat. No.	Std. Pk.	Cat. No.	Std. Pk.
Grey (standard)	CYK4	50	CYDLK4	50	CYDLGK4	50
Blue BU	CYK4/BU	50	CYDLK4/BU	50	CYDLGK4/BU	50
Black BL	CYK4/BL	50	CYDLK4/BL	50	CYDLGK4/BL	50

Additional colors available.



Accessories

	Cat. No.	Std. Pk.	Cat. No.	Std. Pk.	Cat. No.	Std. Pk.
DIN Rail	2511120	20	2511120	20	2511120	20
	CA701-15/S	20	CA701-15/S	20	CA701-15/S	20
End Stop	CA702	50	CA702	50	CA702	50
	CA802	50	CA802	50	CA802	50
	CA202	50	CA202	50	CA202	50
Shorting Link/ Jumpers	JX4/2	100	JX4/2	100	JX4/2	100
	JX4/3	50	JX4/3	50	JX4/3	50
	JX4/4	50	JX4/4	50	JX4/4	50
	—	—	—	—	—	—
	—	—	—	—	—	—
	—	—	—	—	—	—
	JX4/8	10	JX4/8	10	JX4/8	10
	JX4/10	10	JX4/10	10	JX4/10	10
	JX4/16	10	JX4/16	10	JX4/16	10
Marking Tag	MT6	1 Pk. (100 tags)	MT6	1 Pk. (100 tags)	MT6	1 Pk. (100 tags)
Warning Label	WLX4	1 Pk. (100 tags)	WLX4	1 Pk. (100 tags)	WLX4	1 Pk. (100 tags)



CYK4 Disconnect Assembly

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Altech:](#)

[CYDLGK4](#) [CYDLK4](#)