

Intelligent Keyed Safety and Limit Switches


ASI ENK

The ASI ENKK VTU with separate actuator is a very tough standard switch often used for monitoring safety gates and guards.

The enclosure and cover are made from fiber glass-reinforced thermoplastic.

LEDs that indicate the status of the ASI slave and bus are integrated in the cover.

Protection class IP65 in accordance with IEC/EN 60529 is guaranteed.



M12-connection

607.3504.025
ASI ENK VTU

—
—

Direct connection


607.3504.038
ASI ENK VTU D

—
—

ASI Ti2

The Ti2 family with its extremely compact dimensions is the only ASI switch family in this class.

The captive snap-on cover contributes to the protection rating of IP65 in accordance with EN 60529, DIN VED 0470 T1.



M12-connection

607.3401.018
ASI Ti2 w

607.3402.019
ASI Ti2 Riw

607.3403.020
ASI Ti2 Hw

Direct connection

607.3401.033
ASI Ti2 W D

607.3402.034
ASI Ti2 RiW D

607.3403.035
ASI Ti2 HW D


ASI I88

The ASI I88 conforming to EN 50047 is a standard switch used in a wide range of applications.

The enclosure and cover are made from fiber glass-reinforced thermoplastic.

LEDs that indicate the status of the ASI slave and bus are integrated in the cover.

Protection class IP65 in accordance with IEC/EN 60529 is guaranteed.



M12-connection

607.3301.015
ASI I88 w

607.3302.016
ASI I88 RiWk

607.3303.017
ASI I88 Hw

Direct connection

607.3301.030
ASI I88 W D

607.3302.031
ASI I88 RIWK D

607.3303.032
ASI I88 HW D

Drawing dimensions in mm

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Altech:](#)

[607.3303.017](#) [607.3301.030](#) [607.3302.031](#) [607.3402.019](#) [607.3403.020](#) [607.3302.016](#) [607.3504.025](#)
[607.3401.018](#) [607.3403.035](#) [607.3301.015](#) [607.3402.034](#) [607.3504.038](#)