

# Manual Motor Starters

## MMS Series

**Altech Corp.**®



UL508 Type E  
E252942



MMS-32H



MMS-63H



MMS-100H

Part No.		Rated Operational Current	Thermal Release Adjustment Range	Magnetic Release Operating Current	Horsepower Rating						Interrupting Capacity [kA]		
					Single Phase		Three Phase						
					115V	230V	200V	230V	460V	575V	240V	480V	600V
MMS-32H	MMS-32H-0.16A	0.16A	0.1....0.16A	2.1A	-	-	-	-	-	-	100	65	25
	MMS-32H-0.25A	0.25A	0.16....0.25A	3.3A	-	-	-	-	-	-	100	65	25
	MMS-32H-0.4A	0.4A	0.25....0.4A	5.2A	-	-	-	-	-	-	100	65	25
	MMS-32H-0.63A	0.63A	0.4....0.63A	8.2A	-	-	-	-	-	-	100	65	25
	MMS-32H-1.0A	1.0A	0.63....1.0A	13A	-	-	-	-	-	1/2	100	65	25
	MMS-32H-1.6A	1.6A	1.0....1.6A	20.8A	-	1/10	-	-	3/4	3/4	100	65	25
	MMS-32H-2.5A	2.5A	1.6....2.5A	32.5A	-	1/6	1/2	1/2	1	1 1/2	100	65	25
	MMS-32H-4.0A	4.0A	2.5....4.0A	52A	1/8	1/3	3/4	3/4	2	3	100	65	25
	MMS-32H-6A	6A	4....6A	78A	1/4	1/2	1	1 1/2	3	5	100	65	25
	MMS-32H-8A	8A	5....8A	104A	1/3	1	2	2	5	5	100	65	25
	MMS-32H-10A	10A	6....10A	130A	1/2	1 1/2	2	3	5	7 1/2	100	65	25
	MMS-32H-13A	13A	9....13A	169A	1/2	2	3	3	7 1/2	10	100	65	25
	MMS-32H-17A	17A	11....17A	221A	1	3	3	5	10	15	100	30	10
	MMS-32H-22A	22A	14....22A	286A	1 1/2	3	5	7 1/2	15	20	100	30	10
	MMS-32H-26A	26A	18....26A	338A	2	3	7 1/2	7 1/2	15	20	100	30	10
	MMS-32H-32A	32A	22....32A	416A	2	5	7 1/2	10	20	30	100	30	10
MMS-32H-40A	40A	28....40A	520A	3	7 1/2	10	15	30	40	100	30	10	
MMS-63H	MMS-63H-10A	10A	6....10A	130A	1/2	1 1/2	2	3	5	7 1/2	100	65	25
	MMS-63H-13A	13A	9....13A	169A	1/2	2	3	3	7 1/2	10	100	65	25
	MMS-63H-17A	17A	11....17A	221A	1	3	3	5	10	15	100	50	10
	MMS-63H-22A	22A	14....22A	286A	1 1/2	3	5	7 1/2	15	20	100	50	10
	MMS-63H-26A	26A	18....26A	338A	2	3	7 1/2	7 1/2	15	20	100	50	10
	MMS-63H-32A	32A	22....32A	416A	2	5	7 1/2	10	20	30	100	50	10
	MMS-63H-40A	40A	28....40A	520A	3	7 1/2	10	10	30	30	100	50	10
	MMS-63H-50A	50A	34....50A	650A	3	10	15	15	30	40	100	50	10
	MMS-63H-63A	63A	45....63A	819A	5	10	20	20	40	60	100	50	10
	MMS-63H-65A	65A	47....65A	845A	5	15	20	25	50	60	100	50	10
MMS-100H	MMS-100H-17A	17A	11....17A	221A	1	3	3	5	10	15	100	65	25
	MMS-100H-22A	22A	14....22A	286A	1 1/2	3	5	7 1/2	15	20	100	65	25
	MMS-100H-26A	26A	18....26A	338A	2	3	7 1/2	7 1/2	15	20	100	65	25
	MMS-100H-32A	32A	22....32A	416A	2	5	7 1/2	10	20	30	100	65	20
	MMS-100H-40A	40A	28....40A	520A	3	7 1/2	10	10	30	30	100	65	20
	MMS-100H-50A	50A	34....50A	650A	3	10	15	15	30	40	100	65	20
	MMS-100H-63A	63A	45....63A	819A	5	10	20	20	40	60	100	50	10
	MMS-100H-75A	75A	55....75A	975A	5	15	20	25	50	60	100	50	10
	MMS-100H-90A	90A	70....90A	1170A	7 1/2	20	25	30	60	75	100	50	10
	MMS-100H-100A	100A	80....100A	1300A	10	20	30	30	75	100	100	50	10

Drawings and other technical information can be found on page 24-25.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Altech:

[MMS-100H-32A](#) [MMS-32H-22A](#) [MMS-32H-6A](#) [MMS-32H-0.25A](#) [MMS-100H-26A](#) [MMS-63H-32A](#) [MMS-32H-0.16A](#)  
[MMS-100H-22A](#) [MMS-63H-50A](#) [MMS-63H-17A](#) [MMS-100H-75A](#) [MMS-100H-50A](#) [MMS-32H-13A](#) [MMS-63H-40A](#)  
[MMS-63H-10A](#) [MMS-32H-8A](#) [MMS-100H-100A](#) [MMS-63H-63A](#) [MMS-100H-90A](#) [MMS-32H-0.4A](#) [MMS-32H-32A](#)  
[MMS-100H-40A](#) [MMS-100H-17A](#) [MMS-63H-13A](#) [MMS-32H-17A](#) [MMS-63H-26A](#) [MMS-32H-0.63A](#) [MMS-32H-26A](#)  
[MMS-100H-63A](#) [MMS-32H-2.5A](#) [MMS-63H-22A](#) [MMS-63H-65A](#) [MMS-32H-1.6A](#) [MMS-32H-10A](#) [MMS-32H-4.0A](#)  
[MMS-32H-1.0A](#) [MMS-32H-40A](#)