

Contactor

3 Pole / Frame Size 100AF



Altech Corp.

includes 2 x UA-1-11
Auxiliary switch,
(2NO/2NC)

Additional Auxiliaries
and other accessories
see page 11-13

100AF

Type	MC-75A*	MC-85A*	MC-100A*
Number of Poles	3	3	3
NEMA Size	2	3	3
Standard Auxiliaries	2NO/2NC	2NO/2NC	2NO/2NC

	Coil Voltage	Frequency	Part. No.	Part. No.	Part. No.
AC Coil	24V	50/60 Hz	MC-75A-AC24V	MC-85A-AC24V	MC-100A-AC24V
	120V	50/60 Hz	MC-75A-AC120V	MC-85A-AC120V	MC-100A-AC120V
	208V	60 Hz	MC-75A-AC208V	MC-85A-AC208V	MC-100A-AC208V
	230V	50/60 Hz	MC-75A-AC230V	MC-85A-AC230V	MC-100A-AC230V
	480V	60 Hz	MC-75A-AC480V	MC-85A-AC480V	MC-100A-AC480V

Other AC Coil Voltages Available:

60 Hz: 277V, 600V

50/ 60Hz: 48V, 100V, 110V, 200V, 220V, 240V, 380V, 415V, 440V, 500V, 550V

DC Coil	12V	—	MC-75A-DC12V	MC-85A-DC12V	MC-100A-DC12V
	24V	—	MC-75A-DC24V	MC-85A-DC24V	MC-100A-DC24V

Other DC Coil Voltages Available:

20V, 48V, 60V, 80V, 100V, 110V, 125V, 200V, 220V, 250V

HP Rating / UL508

		HP	HP	HP
	Continuous current	110A	135A	160A
Single phase	110~120V	5	7.5	10
	220~240V	15	15	20
Three phase	200~208V	25	30	30
	220~240V	30	40	40
	440~480V	50	60	75
	550~600V	60	75	75

Overload Relays

(Class 10A,
Differential Typical)



MT-95

Setting Ranges (A)

Frame Size 100AF

7-10A	MT-95/3K-10
9-13A	MT-95/3K-13
12-18A	MT-95/3K-18
16-22A	MT-95/3K-22
18-25A	MT-95/3K-25
22-32A	MT-95/3K-32
24-36A	MT-95/3K-36
28-40A	MT-95/3K-40
34-50A	MT-95/3K-50
45-65A	MT-95/3K-65
54-75A	MT-95/3K-75
63-85A	MT-95/3K-85
70-95A	MT-95/3K-95
80-100A	MT-95/3K-100

* Lug terminals available; please add "L" to part number, e.g. MC-75A-AC24V-L.

Drawings and other technical information can be found on page 14-20.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Altech:

[MT-95/3K-75](#) [MC-85A-DC24V](#) [MT-95/3K-36](#) [MT-95/3K-100](#) [MT-95/3K-65](#) [MT-95/3K-13](#) [MT-95/3K-40](#) [MT-95/3K-85](#)
[MT-95/3K-32](#) [MT-95/3K-95](#) [MT-95/3K-25](#) [MT-95/3K-10](#) [MT-95/3K-50](#) [MT-95/3K-18](#) [MT-95/3K-22](#) [MC-75A-AC230V](#)
[MC-75A-AC230V-L](#) [MC-100A-AC120V](#) [MC-100A-AC120V-L](#) [MC-100A-AC208V](#) [MC-100A-AC208V-L](#) [MC-100A-](#)
[AC230V](#) [MC-100A-AC230V-L](#) [MC-85A-AC120V](#) [MC-85A-AC480V](#) [MC-85A-DC12V](#) [MC-85A-DC24V-L](#) [MC-75A-](#)
[DC12V-L](#) [MC-75A-DC24V](#) [MC-75A-DC24V-L](#) [MC-75A-DC12V](#) [MC-85A-AC120V-L](#) [MC-85A-AC208V](#) [MC-85A-](#)
[AC230V](#) [MC-85A-AC230V-L](#) [MC-85A-AC24V](#) [MC-75A-AC120V](#) [MC-75A-AC120V-L](#) [MC-75A-AC208V](#) [MC-75A-](#)
[AC24V](#) [MC-75A-AC24V-L](#) [MC-75A-AC480V](#) [MC-100A-AC24V](#) [MC-100A-AC480V](#) [MC-100A-AC480V-L](#) [MC-100A-](#)
[DC12V](#) [MC-100A-DC24V](#) [MC-100A-DC24V-L](#) [MT-95/3K-75L](#) [MT-95/3K-40L](#) [MT-95/3K-95L](#) [MT-95/3K-85L](#) [MT-](#)
[95/3K-100L](#) [MT-95/3K-65L](#) [MC-75A-AC208V-L](#) [MC-85A-AC480V-L](#)