





Name
Order number
Switching distance
Mounting

KJ15-M30MN40-ANI
08310000294
from 3 mm to 15 mm

Switch type


 non shielded

Signal Type
Connection

 analog
analog current

Connection diagramm

 Cable



fine-pitch thread M30 x 40

Dimension (in mm)
Technical Specification
Special features
Operating voltage
Max. ripple
No load current
Switching frequency
Operating temperature
Temperature drift
Repeat accuracy
Linearity
Analog output
Time delay
Resolution
Reverse voltage protection
Protection category
EMC-level
Housing material
Material active face
Cable length

Output Current 4 ... 20 mA
11 - 35 VDC
 $\leq 5 \%$
 $\leq 10 \text{ mA}$
150 Hz
-25 ° C to 70 ° C
 $\pm 5 \%$
 $\leq 1 \%$
 $\leq 5 \%$
Pulso_has-1
300 ms
1,33 mA / mm
yes
IP67
DIN EN 60947-5-7:2004-06
Brass, nickel plated
PCB
2 m



KJ15-M30MN40-ANI

Pulsotronic GmbH & Co. KG Neue Schichtstraße 14b 09366 Niederdorf Deutschland +49 (0)37296 930-200

Utilisation category
Cable material
Nominal operating voltage
Cable cross
internal load resistor

DC 13
PVC LIYY grau (grey)
24 V DC
3x0.34 mm²

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Altech:](#)

[08310000294](#)