

[Article Page](#)

Product Description

Name
Order number
Matchcode
Switching distance
Mounting

inductive sensor AC/DC
KJ20-Q40KB-VZU
08317730000
9873-0000
20 mm

 shielded

Switch type

 Switchable

Signal Type
Connection
Dimension (in mm)
Technical Specification

AC/DC
Terminal
Q 40 x 40 x 120

Operating voltage
Voltage drop
Max. load current
Leakage current
Switching frequency
Switching hysteresis
Operating temperature
Temperature drift
Repeat accuracy

20 - 250 V AC/DC
5 V
400 mA
≤ 2 mA
15
≤ 15 %
-25 ° C to 70 ° C
≤ 10 %
≤ 5 %

Operating state
Switching state

LED
LED

Digital output
Short-circuit proof
Overload protection
Reverse voltage protection
Protection category
EMC-level
Housing material
Termination

yes
yes
yes
IP67
DIN EN 60947-5-2:2008
PA 6.6
Terminal 1,5mm²

Errors and omissions excepted

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Altech:](#)

[08317730000](#)