






Name
Order number
Switching distance
Mounting

KJ2-M8EB30-DNÖ-V1
08313080241
2 mm



shielded

Switch type



N.C.


DC NPN

Signal Type
Connection



Connector

Connection diagramm



fine-pitch thread M8x1 x 30

Dimension (in mm)
Technical Specification
Operating voltage
Max. ripple
Voltage drop
Max. load current
No load current
Leakage current
Switching frequency
Switching hysteresis
Operating temperature
Temperature drift
Repeat accuracy
Switching state
Short-circuit proof
Overload protection
Reverse voltage protection
Protection category
EMC-level
Housing material
Material active face
Utilisation category

10 - 30 VDC
≤ 10 %
2,4 V
200 mA
≤ 10 mA
≤ 10 μA
2000 Hz
15 %
-25 ° C to 70 ° C
10 %
≤ 5 %
LED
yes
yes
yes
IP 67
DIN EN 60947-5-2:2008
Stainless steel V2A
PBT
DC 13



KJ2-M8EB30-DNÖ-V1

Pulsotronic GmbH & Co. KG Neue Schichtstraße 14b 09366 Niederdorf Deutschland +49 (0)37296 930-200

Termination

Connector M8 3pol

Errors and omissions excepted

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Altech:](#)

[08313080241](#)