## Receptacles

#### Features:

- DIN Rail, Panel Mount or Wall Mount
- Rating: 15A/125V AC • Finger Protection: IP54
- Available in 3 colors.

### **PANEL MOUNT**

### **WALL MOUNT**

### **DIN RAIL MOUNT**







58.5 x 84 x 53.5

10 mm Thermoplastic

External Dimension (HxWxL mm)
Stripping Length
Insulation Material
Type of Connection
Approvals*

36.5 x 61.5 x 50
10 mm
Thermoplastic
3 screw clamps
c <b>(UL</b> )us E154664
125 V
15 A

10 mm	
Thermoplastic	
3 screw clamps	
c <b>Ü</b> L us E154664	
125 V	
15 A	

50 x 71 x 53.5

3 screw clamps
c <b>UL</b> us E154664
125 V
15 A

Std. Pk.

Cat. No.

**DMRBU** DMRGR

Blue Gray Black
Optional Accessory Sealing Gasket

for Panel Mount Receptacles

Voltage Rating **Current Rating** 

Complete Kit:

PMRBU	1	
PMRGR	1	
PMRBA	1	
SEALGASK	1	

Std. Pk.

Cat. No.

WMRBU	1	
WMRGR	1	
WMRBA	1	
Includes Sea	ling Gasket	

Std. Pk.

Cat. No.

DIVIRBA		1	
Includes	Sealing (	Gasket	
	J .		

<sup>\*</sup>UL approval applies to outlet only, not enclosure or DIN rail clip.

# **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

### Altech:

DMRBA DMRBU DMRGR PMRBA PMRBU PMRGR WMRBA WMRBU WMRGR