


Pin Spacing: 3.50mm
 Orientation: Vertical
 Clamp Type: Rising Clamp
 Design: Single Mold


PVPxx-3.50
ELECTRICAL

	Current	Voltage	Wire Range
	8A	300V	—
	8A	130V	—


INSTALLATION DATA

Screw Size	—	PCB Hole Size	1.3mm
Torque	—	Stripping Lgth.	—


MATERIAL

Body	Polyamide	Screw	—
Flammability Class	UL94V-0	Terminal	Tin-Plated Brass
Temperature Limit	105°C UL 125°C IEC	Clamp	—
Color	Green		

No. Poles	Cat. #	Length (mm)	Std. Pk.
2	PVP02-3.50	7.8	100
3	PVP03-3.50	11.3	100
4	PVP04-3.50	14.8	50
5	PVP05-3.50	18.3	50
6	PVP06-3.50	21.8	50
7	PVP07-3.50	25.3	50
8	PVP08-3.50	28.8	50
9	PVP09-3.50	32.3	50
10	PVP10-3.50	35.8	50
11	PVP11-3.50	39.3	50
12	PVP12-3.50	42.8	50
13	PVP13-3.50	46.3	20
14	PVP14-3.50	49.8	20
15	PVP15-3.50	53.3	20
16	PVP16-3.50	56.8	20
17	PVP17-3.50	60.3	20
18	PVP18-3.50	63.8	20
19	PVP19-3.50	67.3	20
20	PVP20-3.50	70.8	20
21	PVP21-3.50	74.3	20
22	PVP22-3.50	77.8	20
23	PVP23-3.50	81.3	20
24	PVP24-3.50	84.8	20



Pin Spacing: 3.50mm
 Orientation: Horizontal Header
 Clamp Type: —
 Design: Single Mold - Closed End


PHPxx-3.50
ELECTRICAL

	Current	Voltage	Wire Range
	8A	300V	—
	8A	130V	—


INSTALLATION DATA

Screw Size	—	PCB Hole Size	1.3mm
Torque	—	Stripping Lgth.	—

MATERIAL

Body	Polyamide	Screw	—
Flammability Class	UL94V-0	Terminal	Tin-Plated Brass
Temperature Limit	105°C UL 125°C IEC	Clamp	—
Color	Green		

No. Poles	Cat. #	Length (mm)	Std. Pk.
2	PHP02-3.50	7.8	100
3	PHP03-3.50	11.3	100
4	PHP04-3.50	14.8	50
5	PHP05-3.50	18.3	50
6	PHP06-3.50	21.8	50
7	PHP07-3.50	25.3	50
8	PHP08-3.50	28.8	50
9	PHP09-3.50	32.3	50
10	PHP10-3.50	35.8	50
11	PHP11-3.50	39.3	50
12	PHP12-3.50	42.8	50
13	PHP13-3.50	46.3	20
14	PHP14-3.50	49.8	20
15	PHP15-3.50	53.3	20
16	PHP16-3.50	56.8	20
17	PHP17-3.50	60.3	20
18	PHP18-3.50	63.8	20
19	PHP19-3.50	67.3	20
20	PHP20-3.50	70.8	20
21	PHP21-3.50	74.3	20
22	PHP22-3.50	77.8	20
23	PHP23-3.50	81.3	20
24	PHP24-3.50	84.8	20



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Altech:

[PVP02-3,50](#) [PVP03-3,50](#) [PVP04-3,50](#) [PVP05-3,50](#) [PVP06-3,50](#) [PVP07-3,50](#) [PVP08-3,50](#) [PVP09-3,50](#) [PVP10-3,50](#) [PVP11-3,50](#) [PVP12-3,50](#) [PVP13-3,50](#) [PVP14-3,50](#) [PVP15-3,50](#) [PVP16-3,50](#) [PVP17-3,50](#) [PVP18-3,50](#) [PVP19-3,50](#) [PVP20-3,50](#) [PVP21-3,50](#) [PVP22-3,50](#) [PVP23-3,50](#) [PVP24-3,50](#)