


5.00mm Pin Spacing – Pluggable PCB Blocks

Pin Spacing: 5.00mm
Orientation: Vertical Header
Clamp Type: –
Design: Single Mold - Closed End



PVPxx-5.00

ELECTRICAL

	Current	Voltage	Wire Range
	12A	300V	–
	16A	450V	–


INSTALLATION DATA

Screw Size	–	PCB Hole Size	1.5mm
Torque	–	Stripping Lgth.	–


MATERIAL

Body	Polyamide	Screw	–
Flammability Class	UL94V-0	Terminal	Tin-Plated Brass
Temperature Limit	105°C UL 125°C IEC	Clamp	–
Color	Green		

No. Poles	Cat. #	Length (mm)	Std. Pk.
2	PVP02-5.00	12.0	100
3	PVP03-5.00	17.0	100
4	PVP04-5.00	22.0	50
5	PVP05-5.00	27.0	50
6	PVP06-5.00	32.0	50
7	PVP07-5.00	37.0	50
8	PVP08-5.00	42.0	50
9	PVP09-5.00	47.0	50
10	PVP10-5.00	52.0	50
11	PVP11-5.00	57.0	50
12	PVP12-5.00	62.0	50
13	PVP13-5.00	67.0	20
14	PVP14-5.00	72.0	20
15	PVP15-5.00	77.0	20
16	PVP16-5.00	82.0	20
17	PVP17-5.00	87.0	20
18	PVP18-5.00	92.0	20
19	PVP19-5.00	97.0	20
20	PVP20-5.00	102.0	20
21	PVP21-5.00	107.0	20
22	PVP22-5.00	112.0	20
23	PVP23-5.00	117.0	20
24	PVP24-5.00	122.0	20



Pin Spacing: 5.00mm
Orientation: Horizontal Header
Clamp Type: –
Design: Single Mold - Closed End



PHPxx-5.00

ELECTRICAL

	Current	Voltage	Wire Range
	12A	300V	–
	16A	450V	–


INSTALLATION DATA

Screw Size	–	PCB Hole Size	1.5mm
Torque	–	Stripping Lgth.	–

MATERIAL

Body	Polyamide	Screw	–
Flammability Class	UL94V-0	Terminal	Tin-Plated Brass
Temperature Limit	105°C UL 125°C IEC	Clamp	–
Color	Green		

No. Poles	Cat. #	Length (mm)	Std. Pk.
2	PHP02-5.00	12.0	100
3	PHP03-5.00	17.0	100
4	PHP04-5.00	22.0	50
5	PHP05-5.00	27.0	50
6	PHP06-5.00	32.0	50
7	PHP07-5.00	37.0	50
8	PHP08-5.00	42.0	50
9	PHP09-5.00	47.0	50
10	PHP10-5.00	52.0	50
11	PHP11-5.00	57.0	50
12	PHP12-5.00	62.0	50
13	PHP13-5.00	67.0	20
14	PHP14-5.00	72.0	20
15	PHP15-5.00	77.0	20
16	PHP16-5.00	82.0	20
17	PHP17-5.00	87.0	20
18	PHP18-5.00	92.0	20
19	PHP19-5.00	97.0	20
20	PHP20-5.00	102.0	20
21	PHP21-5.00	107.0	20
22	PHP22-5.00	112.0	20
23	PHP23-5.00	117.0	20
24	PHP24-5.00	122.0	20



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Altech:

[PVP02-5,00](#) [PHP06-5,00](#) [PHP02-5,00](#) [PHP03-5,00](#) [PHP04-5,00](#) [PHP05-5,00](#) [PHP07-5,00](#) [PHP08-5,00](#) [PHP09-5,00](#) [PHP10-5,00](#) [PHP11-5,00](#) [PHP12-5,00](#) [PHP13-5,00](#) [PHP14-5,00](#) [PHP15-5,00](#) [PHP16-5,00](#) [PHP17-5,00](#) [PHP18-5,00](#) [PHP19-5,00](#) [PHP20-5,00](#) [PHP21-5,00](#) [PHP22-5,00](#) [PHP23-5,00](#) [PHP24-5,00](#) [PVP02-5,00-L](#) [PVP03-5,00](#) [PVP03-5,00-L](#) [PVP04-5,00](#) [PVP04-5,00-L](#) [PVP05-5,00](#) [PVP05-5,00-L](#) [PVP06-5,00](#) [PVP06-5,00-L](#) [PVP07-5,00](#) [PVP07-5,00-L](#) [PVP08-5,00](#) [PVP08-5,00-L](#) [PVP09-5,00](#) [PVP09-5,00-L](#) [PVP10-5,00](#) [PVP10-5,00-L](#) [PVP11-5,00](#) [PVP12-5,00](#) [PVP13-5,00](#) [PVP14-5,00](#) [PVP15-5,00](#) [PVP16-5,00](#) [PVP17-5,00](#) [PVP18-5,00](#) [PVP19-5,00](#) [PVP20-5,00](#) [PVP21-5,00](#) [PVP22-5,00](#) [PVP23-5,00](#) [PVP24-5,00](#)