


























AGT2.5/4		AGT4		AGT4/3		AGT4/4		AGT6/3	
									
5 mm		6 mm		6 mm		6 mm		8 mm	
42 x 54 mm		42 x 61.5 mm		42 x 61.5 mm		42 x 61.5 mm		48 x 74 mm	
12 mm		15 mm		15 mm		15 mm		15 mm	
Polyamide 6.6		Polyamide 6.6		Polyamide 6.6		Polyamide 6.6		Polyamide 6.6	
4 spring clamp connection, grounding through alloy feet		2 spring clamp connection, grounding through alloy feet		3 spring clamp connection, grounding through alloy feet		4 spring clamp connection, grounding through alloy feet		3 spring clamp connection, grounding through alloy feet	
									
22-12 AWG	0.34-2.5 sq.mm.	22-12 AWG	0.2-4 sq.mm.	22-10 AWG	0.2-4 sq.mm.	22-10 AWG	0.2-4 sq.mm.	22-10 AWG	0.2-6 sq.mm.
800V						800V		800V	
24A						32A		32A	
									
Cat. No.	Std. Pk.	Cat. No.	Std. Pk.	Cat. No.	Std. Pk.	Cat. No.	Std. Pk.	Cat. No.	Std. Pk.
<b>AGT2.5/4</b>	100	<b>AGT4</b>	100	<b>AGT4/3</b>	50	<b>AGT4/4</b>	50	<b>AGT6/3</b>	50
EPAS2.5	50	EPAS4	50	EPAS4	50	EPAS4	50	EPAS6	50
									
MT5	100	MT6	100	MT6	100	MT6	100	MT8	100

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Altech:](#)

[AGT2.5/4](#) [AGT4](#) [AGT4/3](#) [AGT4/4](#) [AGT6/3](#)