

**MODEL:** CMS-3648-158SP | **DESCRIPTION:** SPEAKER**FEATURES**

- 8 ohm
- rated 1.5 W
- solder pads
- IPX5

**SPECIFICATIONS**

parameter	conditions/description	min	typ	max	units
input power			1.5	2	W
impedance		6.8	8	9.2	Ω
resonant frequency (Fo)		480	600	720	Hz
frequency response		Fo		14,000	Hz
sound pressure level	at 1.0 W, 50 cm, avg 0.8, 1.0, 1.2, 1.5 kHz	89	92	95	dB
	at 1.0 W, 100 cm, avg 0.8, 1.0, 1.2, 1.5 kHz	83	86	89	dB
distortion	at 1.0 kHz, 1.0 W, 50 cm			5	%
buzz, rattle, etc.	must be normal at sine wave, frequency range			3.46	V
polarity	cone moves forward w/ positive dc current to "+" terminal				
dimensions	$\varnothing 36 \times 4.8$				mm
magnet	Nd-Fe-B				
frame material	iron				
cone material	PEN				
terminal	solder pads				
weight			8.2		g
operating temperature		-20		55	$^{\circ}\text{C}$
storage temperature		-25		60	$^{\circ}\text{C}$
hand soldering	for maximum 2 seconds	360		380	$^{\circ}\text{C}$
RoHS	yes				
IP level	IPX5				




Notes: 1. All specifications measured at 15~35 $^{\circ}\text{C}$, humidity at 25~75%, unless otherwise noted.

MECHANICAL DRAWING

units: mm
tolerance: ± 0.2 mm

MOUNTING NOTICE

AT LEAST
0.8mm
FOR
DIAPHRAGM
MOVING



NOTE:


With Gold plated contact pads

There is no any tin / solder on this Gold plated contact pads

The centre of diaphragm can't exceed the gasket ring

MECHANICAL DRAWING (CONTINUED)


units: mm
tolerance:
 $X \leq 8$: ± 0.15 mm
 $8 < X \leq 16$: ± 0.20 mm
 $16 < X \leq 24$: ± 0.30 mm
unless otherwise specified



RESPONSE CURVES (AT 50 CM)


Frequency Response Curve

Test Conditions: 2.83V / 50 cm



Total Harmonic Distortion Curve


Test Conditions: 2.83V / 50 cm



RESPONSE CURVES (AT 100 CM)


Frequency Response Curve

Test Conditions: 2.83 V / 100 cm



Total Harmonic Distortion Curve

Test Conditions: 2.83 V / 100 cm



REVISION HISTORY

rev.	description	date
1.0	initial release	07/11/2023
1.01	CUI Devices rebranded to Same Sky	09/11/2024

The revision history provided is for informational purposes only and is believed to be accurate.



Same Sky offers a one (1) year limited warranty. Complete warranty information is listed on our website.

Same Sky reserves the right to make changes to the product at any time without notice. Information provided by Same Sky is believed to be accurate and reliable. However, no responsibility is assumed by Same Sky for its use, nor for any infringements of patents or other rights of third parties which may result from its use.

Same Sky products are not authorized or warranted for use as critical components in equipment that requires an extremely high level of reliability. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

sameskydevices.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Same Sky:](#)

[CMS-3648-158SP](#)