





#4-40 X 7/16" FILLISTER HEAD MACHINE SCREW
MATERIAL - STEEL
FINISH - BRIGHT ZINC
QTY: 2 EACH




#4-40 #2 BLANK HEX NUT
MATERIAL - STEEL
FINISH - BRIGHT ZINC
QTY: 2 EACH



#4-40 X 1/2" FILLISTER HEAD CAPTIVE SCREW
MATERIAL - STEEL
FINISH - BRIGHT ZINC
QTY: 2 EACH



#4 SADDLE WASHER
MATERIAL - STEEL
FINISH - BRIGHT ZINC
QTY: 2 EACH



JACKET INSERT TREE
QTY: 1

REVISIONS				
ZONE	REV	DESCRIPTION	DATE	APPROVED
	A	ECN 0607	10-AUG-06	
	B	ECN 0758	19-NOV-14	
	C	ECN 0817	27-SEP-20	
	D	ECN 0845	19-FEB-24	

FILLISTER HEAD CAPTIVE SCREW

THREAD (A)	LENGTH (B)	HEAD STYLE	MATERIAL	PLATING
#4-40 UNC	1/2 INCH	SLOT	COLD ROLL STEEL	ZINC
#4-40 UNC	7/16 INCH	SLOT	COLD ROLL STEEL	ZINC
M2.5 X .45MM	12.7 MM	SLOT	LOW CARBON STEEL	ZINC
M2.6 X .45MM	12.7 MM	SLOT	LOW CARBON STEEL	ZINC
M3 X .5MM	12.7 MM	SLOT	LOW CARBON STEEL	ZINC
#4-40 UNC	1/2 INCH	PHILLIPS	LOW CARBON STEEL	ZINC

CONNECTOR COVER:

- 1.MATERIAL: THERMOPLASTIC UL94V-0
- 2.COLOR: BLACK
- 3.DIMENSIONS: INCHES [MM]
- 4.TOLERANCE: ±0.015 [0.381]

JACKET INSERT TREE

- 1.MATERIAL: POLYPROPYLENE HOMOPOLYMER
- 2.COLOR: BLACK
- 3.DIMENSIONS: INCHES [MM]
- 4.TOLERANCE: ±0.010 [0.254]

UNLESS OTHERWISE SPECIFIED 1. ALL DIMENSIONS ARE IN INCHES (MM) 2. DIMENSIONS ARE TYPICAL		Northern Technologies				THIS DRAWING IS THE PROPERTY OF NORTHERN TECHNOLOGIES AND SHOULD NOT BE REPRODUCED WITHOUT NORTHERN TECHNOLOGIES WRITTEN PERMISSION.	
		PART NUMBER SEE PART NUMBER INFORMATION DESCRIPTION CPP 09 STR EXIT TWO PIECE PLASTIC COVER					
DRAWN JSD	27-APR-05	SIZE B	CODE 200_122	DWG NO. 0002-200-122		REV D	
CHECKED SCN	27-APR-05	SCALE 1:1				SHEET 1 OF 2	
ISSUED	01-SEP-05						

BLACK - PART NUMBER ORDER INFORMATION		
PART#	WITH #4-40 X 1/2" MATING SCREWS (SLOT HEAD)	SUPPLIED
A30E300004	NO LOGO COVER TOP	BULK
A30E301004	NORTECH LOGO COVER TOP	BULK
A30E300104	COVER BOTTOM	BULK
C88E300004	NO LOGO	PACKAGED
C88E301004	NORTECH LOGO	PACKAGED
PART#	WITH #4-40 X 7/16" MATING SCREWS (SLOT HEAD)	SUPPLIED
A30E3000041	NO LOGO COVER TOP	BULK
A30E3010041	NORTECH LOGO COVER TOP	BULK
A30E300104	COVER BOTTOM	BULK
C88E3000041	NO LOGO	PACKAGED
C88E3010041	NORTECH LOGO	PACKAGED
PART#	WITH M2.5 X 12.7MM MATING SCREWS (SLOT HEAD)	SUPPLIED
A30E300004M25S	NO LOGO COVER TOP	BULK
A30E301004M25S	NORTECH LOGO COVER TOP	BULK
A30E300104	COVER BOTTOM	BULK
C88E300004M25S	NO LOGO	PACKAGED
C88E301004M25S	NORTECH LOGO	PACKAGED
PART#	WITH M2.6 X 12.7MM MATING SCREWS (SLOT HEAD)	SUPPLIED
A30E300004M26S	NO LOGO COVER TOP	BULK
A30E301004M26S	NORTECH LOGO COVER TOP	BULK
A30E300104	COVER BOTTOM	BULK
C88E300004M26S	NO LOGO	PACKAGED
C88E301004M26S	NORTECH LOGO	PACKAGED
PART#	WITH M3 X 12.7MM MATING SCREWS (SLOT HEAD)	SUPPLIED
A30E300004M3S	NO LOGO COVER TOP	BULK
A30E301004M3S	NORTECH LOGO COVER TOP	BULK
A30E300104	COVER BOTTOM	BULK
C88E300004M3S	NO LOGO	PACKAGED
C88E301004M3S	NORTECH LOGO	PACKAGED
PART#	WITH #4-40 X 1/2" MATING SCREWS (PHILLIPS HEAD)	SUPPLIED
A30E300004PS	NO LOGO COVER TOP	BULK
A30E301004PS	NORTECH LOGO COVER TOP	BULK
A30E300104	COVER BOTTOM	BULK
C88E300004PS	NO LOGO	PACKAGED
C88E301004PS	NORTECH LOGO	PACKAGED

GRAY - THESE PARTS ARE DISCONTINUED		
PART#	WITH #4-40 X 1/2" MATING SCREWS (SLOT HEAD)	SUPPLIED
A30E300005	NO LOGO COVER TOP	BULK
A30E301005	NORTECH LOGO COVER TOP	BULK
A30E300105	COVER BOTTOM	BULK
C88E300005	NO LOGO	PACKAGED
C88E301005	NORTECH LOGO	PACKAGED
PART#	WITH #4-40 X 7/16" MATING SCREWS (SLOT HEAD)	SUPPLIED
A30E3000051	NO LOGO COVER TOP	BULK
A30E3010051	NORTECH LOGO COVER TOP	BULK
A30E300105	COVER BOTTOM	BULK
C88E3000051	NO LOGO	PACKAGED
C88E3010051	NORTECH LOGO	PACKAGED
PART#	WITH M2.5 X 12.7MM MATING SCREWS (SLOT HEAD)	SUPPLIED
A30E300005M25S	NO LOGO COVER TOP	BULK
A30E301005M25S	NORTECH LOGO COVER TOP	BULK
A30E300105	COVER BOTTOM	BULK
C88E300005M25S	NO LOGO	PACKAGED
C88E301005M25S	NORTECH LOGO	PACKAGED
PART#	WITH M2.6 X 12.7MM MATING SCREWS (SLOT HEAD)	SUPPLIED
A30E300005M26S	NO LOGO COVER TOP	BULK
A30E301005M26S	NORTECH LOGO COVER TOP	BULK
A30E300105	COVER BOTTOM	BULK
C88E300005M26S	NO LOGO	PACKAGED
C88E301005M26S	NORTECH LOGO	PACKAGED
PART#	WITH M3 X 12.7MM MATING SCREWS (SLOT HEAD)	SUPPLIED
A30E300005M3S	NO LOGO COVER TOP	BULK
A30E301005M3S	NORTECH LOGO COVER TOP	BULK
A30E300105	COVER BOTTOM	BULK
C88E300005M3S	NO LOGO	PACKAGED
C88E301005M3S	NORTECH LOGO	PACKAGED
PART#	WITH #4-40 X 1/2" MATING SCREWS (PHILLIPS HEAD)	SUPPLIED
A30E300005PS	NO LOGO COVER TOP	BULK
A30E301005PS	NORTECH LOGO COVER TOP	BULK
A30E300105	COVER BOTTOM	BULK
C88E300005PS	NO LOGO	PACKAGED
C88E301005PS	NORTECH LOGO	PACKAGED

NO LOGO

NORTECH LOGO

Northern Technologies

THIS DRAWING IS THE PROPERTY OF NORTHERN TECHNOLOGIES AND SHOULD NOT BE REPRODUCED WITHOUT NORTHERN TECHNOLOGIES WRITTEN PERMISSION.

PART NUMBER SEE PART NUMBER INFORMATION

DESCRIPTION CPP 09 STR EXIT TWO PIECE PLASTIC COVER

SIZE B

CODE 200_122

DWG NO. 0002-200-122

REV D

SCALE 1:1

SHEET 2 OF 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Northern Technologies:](#)

[C88E301004M3S](#) [C88E301004](#)