


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.



REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
E	ECN 81 17: CORRECTED FUNCTION NAMES IN WIRE MAP.	10/1/15	D. DESJARDIN
F	ECN 10639: REMOVED RoHS STATEMENT	08/21/2020	PNEWTON



MODEL NUMBER	LENGTH METERS [FEET]
CMD24-05M	0.5 [1.64]
CMD24-1M	1.0 [3.28]
CMD24-2M	2.0 [6.56]
CMD24-3M	3.0 [9.84]
CMD24-4M	4.0 [13.12]
CMD24-5M	5.0 [16.40]
CMD24-10M	10.0 [32.80]

NOTES:

1. SEE SHEET 2 FOR WIRING MAP.
2. CABLE MEETS REQUIREMENTS OF ANSI/IEEE STD 488.1-1987.
3. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
4. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]		APPROVALS		DATE		 an INFINITI® brand		50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0		DRAWN BY TJC		9/1/01		CATEGORY		IEEE-488	
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [.5] ANGLES ± 1° .XXX = ± .005 [.13]		CHECKED BY DFP		9/5/01					
THIRD-ANGLE PROJECTION 		APPROVED BY		9/10/01					
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		PRODUCT DESCRIPTION		CABLE, MOLD GPIB M/M					
THIRD-ANGLE PROJECTION 		COLOR VARIATIONS MAY OCCUR		SIZE A	CAGE CODE 43321	ITEM NO. CMD24	REV. F		
				SCALE: NONE		CAD FILE: CMD24.SLDDRW		SHEET 1 OF 2	

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE
PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE
WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

WIRING MAP			
PAIR NUMBER	J1/P1	P2	FUNCTION
1	1	1	DATA LINE DI01
	14	14	DATA LINE DI06
2	2	2	DATA LINE DI02
	3	3	DATA LINE DI03
3	4	4	DATA LINE DI04
	13	13	DATA LINE DI05
4	15	15	DATA LINE DI07
	16	16	DATA LINE DI08
5	5	5	EOI
	24	24	EOI RETURN
6	6	6	DAV
	18	18	DAV RETURN
7	7	7	NRFD
	19	19	NRDF RETURN
8	8	8	NDAC
	20	20	NDAC RETURN
9	9	9	IFC
	21	21	IFC RETURN
10	10	10	SRQ
	22	22	SRQ RETURN
11	11	11	ATN
	23	23	ATN RETURN
12	17	17	REN
	24	24	REN RETURN
DRAIN WIRE	12 & SHELL	12 & SHELL	SHIELD

 an INFINITI® brand		50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
CATEGORY			
IEEE-488			
PRODUCT DESCRIPTION			
CABLE, MOLD GPIB M/M			
SIZE A	CAGE CODE 43321	ITEM NO. CMD24	REV. F
SCALE: NONE		CAD FILE: CMD24.SLDDRW	SHEET 2 OF 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[L-Com:](#)

[CMD24-1M](#)