





THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.



REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	12/21/11	D.GRIFFIN
B	ECN8182; UPD DWG FROM MOLDED THUMBSCREW TO METAL THUMBSCREW	11/30/2013	B.ZHANG




MODEL NUMBER	LENGTH	
	FEET	METERS
DVIDDLZ-45-1	1.0	.31
DVIDDLZ-45-3	3.0	.91
DVIDDLZ-45-5	5.0	1.52
DVIDDLZ-45-10	10.0	3.05
DVIDDLZ-45-15	15.0	4.57

- NOTES:**
1. CABLES TO BE TESTED FOR CONTINUITY.
 2. CABLES TO BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.
 3. DUST COVERS INSTALLED FOR SHIPPING (NOT SHOWN).

REGULATORY COMPLIANCE:
CE2011/65/EU(RoHS DIRECTIVE)



UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [1.27] .XXX = ±.005 [0.127] PROJECTION 	APPROVALS	DATE	 Global Connectivity 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	DRAWN BY D.FRISIELLO	12/14/11		
	CHECKED BY R.SCOTT	12/14/11	CATEGORY	
	APPROVED BY P.McNEIL	12/14/11		AUDIO/VIDEO
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	PRODUCT DESCRIPTION		CA DVI-D DL 45 DEG W/FERR LSZH	
	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321	DWG. NO. DVIDDLZ-45
REF	SCALE: NONE	CAD FILE: DVIDDLZ-45.SLDDRW	SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[L-Com:](#)

[DPHD4KA-5M](#)