





THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE
PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE
WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	7/30/13	D.GRIFFIN
B	ECN 9020; REVISE NOTES TO REMOVE HDMI LABEL, NEW DWG FORMAT	12/22/2017	B.ZHANG





HDMI MALE
19 PIN CONNECTOR
GOLD PLATED CONTACTS



SECTION A-A

HDMI MALE
45° LEFT EXIT
19 PIN CONNECTOR
GOLD PLATED CONTACTS




MODEL NO.	LENGTH METERS [FEET]
HDCA453MM-0.5	0.5 [1.64]
HDCA453MM-1	1.0 [3.28]
HDCA453MM-2	2.0 [6.56]
HDCA453MM-3	3.0 [9.84]
HDCA453MM-4	4.0 [13.12]
HDCA453MM-5	5.0 [16.41]

NOTES:

1. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
2. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.
3. DUST COVERS INSTALLED FOR SHIPPING (NOT SHOWN).

REGULATORY COMPLIANCE:
CE2011/65/EU (RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]		APPROVALS	DATE	L-com® Global Connectivity		50 HIGH STREET NORTH ANDOVER, MA 01845	
OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%		DRAWN BY D. DESJARDIN	4/15/13	CATEGORY		AUDIO/VIDEO	
		CHECKED BY D. FRISIELLO	4/15/13				
		APPROVED BY S. SMITH	4/15/13	PRODUCT DESCRIPTION			
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [5.1] .XXX = ±.005 [1.3]		CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		CA HDMI STR TO 45 DEG LEFT EXIT			
PROJECTION 	COLOR VARIATIONS MAY OCCUR		SIZE A	FSCM NO. 43321	DWG. NO. HDCA453MM	REV B	
			SCALE: NONE	CAD FILE: HDCA453MM.SLDDRW	SHEET 1 OF		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[L-Com:](#)

[HD8KA-5M](#)