



N Female Bulkhead to N Male Right Angle Cable 200 cm Length Using PE-SR402FLJ Coax

RF Cable Assemblies Technical Data Sheet


PE3W03365-200CM

Configuration

- Connector 1: N Female Bulkhead
- Connector 2: N Male Right Angle
- Cable Type: PE-SR402FLJ

Features

- Shielding Effectivity > 100 dB
- 70% Phase Velocity
- FEP Jacket



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3W03365-200CM type N female bulkhead to type N male right angle 200 cm cable using PE-SR402FLJ coax is part of our full line of RF components available for same-day shipping. Pasternack's formable RF cable assemblies provide an alternative to costly pre-formed semi-rigid assemblies since they are hand formable. This Pasternack type N to type N cable assembly has a female to male gender configuration with 50 ohm formable PE-SR402FLJ coax. The right angle type N interface on the PE-SR402FLJ cable allows for easier connections in tight spaces. Our RF cable assembly with type N bulkhead interface allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Velocity of Propagation		70		%
RF Shielding	100			dB
Group Delay		1.43 [4.69]		ns/ft [ns/m]
Capacitance		29 [95.14]		pF/ft [pF/m]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [N Female Bulkhead to N Male Right Angle Cable 200 cm Length Using PE-SR402FLJ Coax PE3W03365-200CM](#)



N Female Bulkhead to N Male Right Angle Cable
200 cm Length Using PE-SR402FLJ Coax

RF Cable Assemblies Technical Data Sheet

PE3W03365-200CM

Mechanical Specifications

Cable Assembly

Length* 78.74 in [200 cm]

Cable

Cable Type PE-SR402FLJ
Impedance 50 Ohms
Inner Conductor Type Solid
Inner Conductor Material and Plating Copper Clad Steel, Silver
Dielectric Type PTFE
Number of Shields 1
Shield Layer 1 Tinned Copper Braid
Jacket Material FEP, Black
Jacket Diameter 0.161 in [4.09 mm]

One Time Minimum Bend Radius 0.315 in [8 mm]
Repeated Minimum Bend Radius 1.575 in [40.01 mm]

Connectors

Description	Connector 1	Connector 2
Type	N Female Bulkhead	N Male Right Angle
Impedance	50 Ohms	50 Ohms
Contact Material and Plating		Brass, Gold over Nickel
Dielectric Type		PTFE
Body Material and Plating	Brass, Nickel	Brass, Nickel
Coupling Nut Material and Plating		Brass, Nickel

Mechanical Specification Notes:

*All cable assemblies have a length tolerance of 1.5% or $\pm 3/8"$, whichever is greater.

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [N Female Bulkhead to N Male Right Angle Cable 200 cm Length Using PE-SR402FLJ Coax PE3W03365-200CM](#)



N Female Bulkhead to N Male Right Angle Cable
200 cm Length Using PE-SR402FLJ Coax

RF Cable Assemblies Technical Data Sheet

PE3W03365-200CM

How to Order

Part Number Configuration:

PE3W03365

- xx

uu

Unit of Measure:
cm = Centimeters
<blank> = Inches
Length
Base Number

Example: PE3W03365-12 = 12 inches long cable
PE3W03365-100cm = 100 cm long cable

N Female Bulkhead to N Male Right Angle Cable 200 cm Length Using PE-SR402FLJ Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [N Female Bulkhead to N Male Right Angle Cable 200 cm Length Using PE-SR402FLJ Coax PE3W03365-200CM](#)


URL: <https://www.pasternack.com/n-female-n-male-pe-sr402flj-cable-assembly-pe3w03365-200cm-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE3W03365-200CM CAD Drawing

N Female Bulkhead to N Male Right Angle Cable

200 cm Length Using PE-SR402FLJ Coax



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Pasternack:](#)

[PE3W03365-200CM](#)