


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE
PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE
WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	03/10/2025	BZHANG	DGUST




NOTES:

1. LENGTHS OVER 10 METERS (32.8 FT) ARE CHANNEL RATED.
2. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]		APPROVALS		DATE		L-com[™] an INFINITI[®] brand		50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0		DRAWN BY BZHANG		06/20/2023		CATEGORY		TELECOM/MODULAR	
		CHECKED BY KGLEBOVA		03/13/2025					
		APPROVED BY WLI		06/20/2023					
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] .XX = ± .02 [.5] .XXX = ± .005 [.13]		FRACTIONS ± 1/32 ANGLES ± 1°		CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		PRODUCT DESCRIPTION CBL, RJ45/RJ45 C6A SHLD CMR PVC			
THIRD-ANGLE PROJECTION 		COLOR VARIATIONS MAY OCCUR		SIZE A		CAGE CODE 43321		ITEM NO. TRD695ASR	
						SCALE: NONE		CAD FILE: trd695csr.SLDDRW	
								SHEET 1 OF 3	

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE
PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE
WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

MODEL NUMBER	JACKET COLOR	LENGTH		MODEL NUMBER	JACKET COLOR	LENGTH		MODEL NUMBER	JACKET COLOR	LENGTH	
		METERS	FEET			METERS	FEET			METERS	FEET
TRD695ASR-BLU-1M	BLUE	1.0	3.28	TRD695ASR-RED-1M	RED	1.0	3.28	TRD695ASR-BLK-1M	BLACK	1.0	3.28
TRD695ASR-BLU-2M	BLUE	2.0	6.56	TRD695ASR-RED-2M	RED	2.0	6.56	TRD695ASR-BLK-2M	BLACK	2.0	6.56
TRD695ASR-BLU-3M	BLUE	3.0	9.84	TRD695ASR-RED-3M	RED	3.0	9.84	TRD695ASR-BLK-3M	BLACK	3.0	9.84
TRD695ASR-BLU-4M	BLUE	4.0	13.12	TRD695ASR-RED-4M	RED	4.0	13.12	TRD695ASR-BLK-4M	BLACK	4.0	13.12
TRD695ASR-BLU-5M	BLUE	5.0	16.41	TRD695ASR-RED-5M	RED	5.0	16.41	TRD695ASR-BLK-5M	BLACK	5.0	16.41
TRD695ASR-BLU-7M	BLUE	7.0	22.97	TRD695ASR-RED-7M	RED	7.0	22.97	TRD695ASR-BLK-7M	BLACK	7.0	22.97
TRD695ASR-BLU-10M	BLUE	10.0	32.81	TRD695ASR-RED-10M	RED	10.0	32.81	TRD695ASR-BLK-10M	BLACK	10.0	32.81
TRD695ASR-BLU-12M	BLUE	12.0	39.37	TRD695ASR-RED-12M	RED	12.0	39.37	TRD695ASR-BLK-12M	BLACK	12.0	39.37
TRD695ASR-BLU-15M	BLUE	15.0	49.22	TRD695ASR-RED-15M	RED	15.0	49.22	TRD695ASR-BLK-15M	BLACK	15.0	49.22
TRD695ASR-BLU-20M	BLUE	20.0	65.62	TRD695ASR-RED-20M	RED	20.0	65.62	TRD695ASR-BLK-20M	BLACK	20.0	65.62
TRD695ASR-BLU-25M	BLUE	25.0	82.02	TRD695ASR-RED-25M	RED	25.0	82.02	TRD695ASR-BLK-25M	BLACK	25.0	82.02
TRD695ASR-BLU-30M	BLUE	30.0	98.43	TRD695ASR-RED-30M	RED	30.0	98.43	TRD695ASR-BLK-30M	BLACK	30.0	98.43

 an INFINITI® brand		50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
CATEGORY			
TELECOM/MODULAR			
PRODUCT DESCRIPTION			
CBL, RJ45/RJ45 C6A SHLD CMR PVC			
SIZE	CAGE CODE	ITEM NO.	REV.
A	43321	TRD695ASR	A
SCALE: NONE		CAD FILE: trd695csr.SLDDRW	SHEET 2 OF 3

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE
PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE
WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

MODEL NUMBER	JACKET COLOR	LENGTH		MODEL NUMBER	JACKET COLOR	LENGTH		MODEL NUMBER	JACKET COLOR	LENGTH	
		METERS	FEET			METERS	FEET			METERS	FEET
TRD695ASR-GRN-1M	GREEN	1.0	3.28	TRD695ASR-GRY-1M	GRAY	1.0	3.28	TRD695ASR-YLW-1M	YELLOW	1.0	3.28
TRD695ASR-GRN-2M	GREEN	2.0	6.56	TRD695ASR-GRY-2M	GRAY	2.0	6.56	TRD695ASR-YLW-2M	YELLOW	2.0	6.56
TRD695ASR-GRN-3M	GREEN	3.0	9.84	TRD695ASR-GRY-3M	GRAY	3.0	9.84	TRD695ASR-YLW-3M	YELLOW	3.0	9.84
TRD695ASR-GRN-4M	GREEN	4.0	13.12	TRD695ASR-GRY-4M	GRAY	4.0	13.12	TRD695ASR-YLW-4M	YELLOW	4.0	13.12
TRD695ASR-GRN-5M	GREEN	5.0	16.41	TRD695ASR-GRY-5M	GRAY	5.0	16.41	TRD695ASR-YLW-5M	YELLOW	5.0	16.41
TRD695ASR-GRN-7M	GREEN	7.0	22.97	TRD695ASR-GRY-7M	GRAY	7.0	22.97	TRD695ASR-YLW-7M	YELLOW	7.0	22.97
TRD695ASR-GRN-10M	GREEN	10.0	32.81	TRD695ASR-GRY-10M	GRAY	10.0	32.81	TRD695ASR-YLW-10M	YELLOW	10.0	32.81
TRD695ASR-GRN-12M	GREEN	12.0	39.37	TRD695ASR-GRY-12M	GRAY	12.0	39.37	TRD695ASR-YLW-12M	YELLOW	12.0	39.37
TRD695ASR-GRN-15M	GREEN	15.0	49.22	TRD695ASR-GRY-15M	GRAY	15.0	49.22	TRD695ASR-YLW-15M	YELLOW	15.0	49.22
TRD695ASR-GRN-20M	GREEN	20.0	65.62	TRD695ASR-GRY-20M	GRAY	20.0	65.62	TRD695ASR-YLW-20M	YELLOW	20.0	65.62
TRD695ASR-GRN-25M	GREEN	25.0	82.02	TRD695ASR-GRY-25M	GRAY	25.0	82.02	TRD695ASR-YLW-25M	YELLOW	25.0	82.02
TRD695ASR-GRN-30M	GREEN	30.0	98.43	TRD695ASR-GRY-30M	GRAY	30.0	98.43	TRD695ASR-YLW-30M	YELLOW	30.0	98.43

 an INFINITI® brand		50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
CATEGORY			
TELECOM/MODULAR			
PRODUCT DESCRIPTION			
CBL, RJ45/RJ45 C6A SHLD CMR PVC			
SIZE	CAGE CODE	ITEM NO.	REV.
A	43321	TRD695ASR	A
SCALE: NONE		CAD FILE: trd695csr.SLDDRW	SHEET 3 OF 3

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[L-Com:](#)

[TRD695ASR-BLU-12M](#)