



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE
PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE
WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	03/10/2025	BZHANG	DGUST



NOTES:

1. LENGTHS OVER 10 METERS (32.8 FT) ARE CHANNEL RATED.
2. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

LSZH CABLE CHARACTERISTICS:
FLAME RATING: IEC 60332-1
CORROSIVE GAS: IEC 60754
SMOKE EMISSION: IEC 61034

REGULATORY COMPLIANCE:
EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS .XX = ± .02 [.5] ± 1/32 .XXX = ± .005 [.13] ANGLES ± 1° THIRD-ANGLE PROJECTION 	APPROVALS	DATE	 an INFINITI® brand 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936		
	DRAWN BY BZHANG	06/20/2023		CATEGORY TELECOM/MODULAR	
	CHECKED BY KGLEBOVA	03/13/2025			
	APPROVED BY	06/20/2023			
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		PRODUCT DESCRIPTION CBL, RJ45/RJ45 C6A SHLD CMX LSZH			
COLOR VARIATIONS MAY OCCUR		SIZE A		CAGE CODE 43321	ITEM NO. TRD695ASZX
		SCALE: NONE CAD FILE: trd695aszx.SLDDRW			SHEET 1 OF 2

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE
PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE
WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

MODEL NUMBER	JACKET COLOR	LENGTH		MODEL NUMBER	JACKET COLOR	LENGTH		MODEL NUMBER	JACKET COLOR	LENGTH	
		METERS	FEET			METERS	FEET			METERS	FEET
TRD695ASZX-BLU-1M	BLUE	1.0	3.28	TRD695ASZX-RED-1M	RED	1.0	3.28	TRD695ASZX-BLK-1M	BLACK	1.0	3.28
TRD695ASZX-BLU-2M	BLUE	2.0	6.56	TRD695ASZX-RED-2M	RED	2.0	6.56	TRD695ASZX-BLK-2M	BLACK	2.0	6.56
TRD695ASZX-BLU-3M	BLUE	3.0	9.84	TRD695ASZX-RED-3M	RED	3.0	9.84	TRD695ASZX-BLK-3M	BLACK	3.0	9.84
TRD695ASZX-BLU-4M	BLUE	4.0	13.12	TRD695ASZX-RED-4M	RED	4.0	13.12	TRD695ASZX-BLK-4M	BLACK	4.0	13.12
TRD695ASZX-BLU-5M	BLUE	5.0	16.41	TRD695ASZX-RED-5M	RED	5.0	16.41	TRD695ASZX-BLK-5M	BLACK	5.0	16.41
TRD695ASZX-BLU-7M	BLUE	7.0	22.97	TRD695ASZX-RED-7M	RED	7.0	22.97	TRD695ASZX-BLK-7M	BLACK	7.0	22.97
TRD695ASZX-BLU-10M	BLUE	10.0	32.81	TRD695ASZX-RED-10M	RED	10.0	32.81	TRD695ASZX-BLK-10M	BLACK	10.0	32.81
TRD695ASZX-BLU-12M	BLUE	12.0	39.37	TRD695ASZX-RED-12M	RED	12.0	39.37	TRD695ASZX-BLK-12M	BLACK	12.0	39.37
TRD695ASZX-BLU-15M	BLUE	15.0	49.22	TRD695ASZX-RED-15M	RED	15.0	49.22	TRD695ASZX-BLK-15M	BLACK	15.0	49.22
TRD695ASZX-BLU-20M	BLUE	20.0	65.62	TRD695ASZX-RED-20M	RED	20.0	65.62	TRD695ASZX-BLK-20M	BLACK	20.0	65.62
TRD695ASZX-BLU-25M	BLUE	25.0	82.02	TRD695ASZX-RED-25M	RED	25.0	82.02	TRD695ASZX-BLK-25M	BLACK	25.0	82.02
TRD695ASZX-BLU-30M	BLUE	30.0	98.43	TRD695ASZX-RED-30M	RED	30.0	98.43	TRD695ASZX-BLK-30M	BLACK	30.0	98.43

 an INFINITI® brand			50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
CATEGORY				
TELECOM/MODULAR				
PRODUCT DESCRIPTION				
CBL, RJ45/RJ45 C6A SHLD CMX LSZH				
SIZE	CAGE CODE	ITEM NO.		REV.
A	43321	TRD695ASZX		A
SCALE: NONE		CAD FILE: trd695oszx.SLDDRW		SHEET 2 OF 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[L-Com:](#)

[TRD695ASZX-BLU-12M](#)