

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	05/11/2023	SREITER	GUTTADAURO

D

D

C

C


B

B

A

A



T-Rev.D1



## NOTES:

1. PLUG: TYPE C14, BLACK
2. CONNECTOR: C13 LOCK PLUS, BLACK
3. CORDAGE: SJT3X17/H05VVF3G1.0mm², BLACK
4. FOR REFERENCE ONLY:
  - A. COLOR CODING OF CONDUCTORS: BLUE, BROWN, GREEN/YELLOW
  - B. APPROVALS: ENEC, UL, cUL, SAA
  - C. RATING: 10A/250V
5. OPTIONAL LABELS MAY INCLUDE UL, CURRENT AND/OR WARNING.
6. CABLE ASSEMBLIES SHALL BE INDIVIDUALLY PACKAGED.

TABULATION BLOCK	
ITEM NO.	LENGTH ±.6 [15]
C13LPC14-10-3F	36.0 [914]
C13LPC14-10-6F	72.0 [1829]
C13LPC14-10-10F	120.0 [3048]

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5]   FRACTIONS ± 1/32 .XX = ±.02 [.5]   ANGLES ± 1° .XXX = ±.005 [.13]		APPROVALS	DATE	 an INFINITI® brand 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
		DRAWN BY SREITER	5/11/2023	
		CHECKED BY DGUST	05/11/2023	
		APPROVED BY GUTTADAURO	05/11/2023	
THIRD-ANGLE PROJECTION 		CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		CATEGORY POWER PRODUCTS
COLOR VARIATIONS MAY OCCUR		PRODUCT DESCRIPTION IEC LOCK C13+ TO C14, 10A, 250V		SIZE A
		CAGE CODE 43321	ITEM NO. C13LPC14-10	REV. A
		SCALE: NONE	CAD FILE: C13LPC14-10-10F.SLDDRW	SHEET 1 OF 1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[infinite Electronics:](#)

[C13LPC14-10-10F](#)