



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

RoHS Compliant ✓

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	3/2/12	D.GRIFFIN
B	ECN 6451: UPDATED NOTES & WIRING MAP. CHANGED EXPOSED CONN. DIM.	10/10/12	D. DESJARDIN



MODEL NUMBER	LENGTH METERS [FEET]
CAA-90UMB5-03M	.3 [.98]
CAA-90UMB5-05M	.5 [1.64]
CAA-90UMB5-075M	.75 [2.46]
CAA-90UMB5-1M	1.0 [3.28]
CAA-90UMB5-2M	2.0 [6.56]
CAA-90UMB5-3M	3.0 [9.84]
CAA-90UMB5-5M	5.0 [16.41]



#### NOTES:

1. CABLE ASSEMBLY SHALL HAVE 360° SHIELD TERMINATION.
2. CABLE ASSEMBLY SHALL MEET USB 2.0 REQUIREMENTS.
3. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
4. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005 PROJECTION 	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY D.FRISIELLO	5/17/11	
	CHECKED BY D.CASTRO	5/17/11	CATEGORY
	APPROVED BY S.SMITH	5/17/11	PRODUCT DESCRIPTION
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		USB	
COLOR VARIATIONS MAY OCCUR		SIZE <b>A</b>	FSCM NO. <b>43321</b>
SCALE: NONE		DWG. NO. <b>CAA-90UMB5</b>	REV. <b>B</b>
CAD FILE: CAA-90UMB5.SLDDRW		SHEET 1 OF 1	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[infinite Electronics:](#)

[CAA-90UMB5-075M](#) [CAA-90UMB5-3M](#) [CAA-90UMB5-2M](#) [CAA-90UMB5-1M](#) [CAA-90UMB5-05M](#) [CAA-90UMB5-03M](#) [CAA-90UMB5-5M](#)